

Item description/product images



Description

Material:

Crank and grip thermoplastic.

Hub and grip axle steel, strength class 5.8, or stainless steel 1.4404.

Version:

Thermoplastic black grey.

Steel parts black oxidised.

Stainless steel bright.

Note:

The hub cover is supplied unassembled.

The crank handles can be secured to the shaft by cross-pinning or by parallel key together with a DIN 6912 socket head screw and DIN 7349 washer.

Versions with transverse bore are secured using the ISO 4027 (DIN 914) grub screw.


Accessory:

07161 Cap screws with low head DIN 6912

Drawing reference:


1) Position of the transverse bore to the keyway is offset by 90°.

Drawings



Drawings

DIN 6885-1



Overview of items

Order No.	Version 1	Version 2	Component material	A	D	D2	D7	H	H1	H2	H3	H4	L	L2	B3	SW	T
06500-1108	reamed hole	without transverse hole	steel	80	24	8	-	85,7	49	28,5	13	-	104	12,7	-	-	-
06500-1110	reamed hole	without transverse hole	steel	80	24	10	-	85,7	49	28,5	13	-	104	12,7	-	-	-
06500-1210	reamed hole	without transverse hole	steel	100	29	10	-	105,2	49	35,5	13	-	129	15,7	-	-	-
06500-1212	reamed hole	without transverse hole	steel	100	29	12	-	105,2	59,5	35,5	13	-	129	15,7	-	-	-
06500-1312	reamed hole	without transverse hole	steel	125	36	12	-	140	83	44	18,5	-	161	19,5	-	-	-
06500-1314	reamed hole	without transverse hole	steel	125	36	14	-	140	83	44	18,5	-	161	19,5	-	-	-
06500-11086	reamed hole	with transverse bore	steel	80	24	8	M6	85,7	49	28,5	13	7,5	104	12,7	-	-	-
06500-11106	reamed hole	with transverse bore	steel	80	24	10	M6	85,7	49	28,5	13	7,5	104	12,7	-	-	-
06500-12106	reamed hole	with transverse bore	steel	100	29	10	M6	105,2	59,5	35,5	13	7,5	129	15,7	-	-	-
06500-12126	reamed hole	with transverse bore	steel	100	29	12	M6	105,2	59,5	35,5	13	7,5	129	15,7	-	-	-
06500-13126	reamed hole	with transverse bore	steel	125	36	12	M6	140	83	44	18,5	7,5	161	19,5	-	-	-
06500-13146	reamed hole	with transverse bore	steel	125	36	14	M6	140	83	44	18,5	7,5	161	19,5	-	-	-
06500-01108	reamed hole	without transverse hole	stainless steel	80	24	8	-	85,7	49	28,5	13	-	104	12,7	-	-	-
06500-01110	reamed hole	without transverse hole	stainless steel	80	24	10	-	85,7	49	28,5	13	-	104	12,7	-	-	-
06500-01210	reamed hole	without transverse hole	stainless steel	100	29	10	-	105,2	49	35,5	13	-	129	15,7	-	-	-
06500-01212	reamed hole	without transverse hole	stainless steel	100	29	12	-	105,2	59,5	35,5	13	-	129	15,7	-	-	-
06500-01312	reamed hole	without transverse hole	stainless steel	125	36	12	-	140	83	44	18,5	-	161	19,5	-	-	-
06500-01314	reamed hole	without transverse hole	stainless steel	125	36	14	-	140	83	44	18,5	-	161	19,5	-	-	-
06500-011086	reamed hole	with transverse bore	stainless steel	80	24	8	M6	85,7	49	28,5	13	7,5	104	12,7	-	-	-
06500-011106	reamed hole	with transverse bore	stainless steel	80	24	10	M6	85,7	49	28,5	13	7,5	104	12,7	-	-	-
06500-012106	reamed hole	with transverse bore	stainless steel	100	29	10	M6	105,2	59,5	35,5	13	7,5	129	15,7	-	-	-
06500-012126	reamed hole	with transverse bore	stainless steel	100	29	12	M6	105,2	59,5	35,5	13	7,5	129	15,7	-	-	-
06500-013126	reamed hole	with transverse bore	stainless steel	125	36	12	M6	140	83	44	18,5	7,5	161	19,5	-	-	-
06500-013146	reamed hole	with transverse bore	stainless steel	125	36	14	M6	140	83	44	18,5	7,5	161	19,5	-	-	-
06500-110802	reamed hole with slot	without transverse hole	steel	80	24	8	-	85,7	49	28,5	13	-	104	12,7	2	-	9
06500-111003	reamed hole with slot	without transverse hole	steel	80	24	10	-	85,7	49	28,5	13	-	104	12,7	3	-	11,4
06500-121003	reamed hole with slot	without transverse hole	steel	100	29	10	-	105,2	59,5	35,5	13	-	129	15,7	3	-	11,4
06500-121204	reamed hole with slot	without transverse hole	steel	100	29	12	-	105,2	59,5	35,5	13	-	129	15,7	4	-	13,8
06500-131204	reamed hole with slot	without transverse hole	steel	125	36	12	-	140	83	44	18,5	-	161	19,5	4	-	13,8
06500-131405	reamed hole with slot	without transverse hole	steel	125	36	14	-	140	83	44	18,5	-	161	19,5	5	-	16,3
06500-1108026	reamed hole with slot	with transverse bore	steel	80	24	8	M6	85,7	49	28,5	13	7,5	104	12,7	2	-	9
06500-1110036	reamed hole with slot	with transverse bore	steel	80	24	10	M6	85,7	49	28,5	13	7,5	104	12,7	3	-	11,4
06500-1210036	reamed hole with slot	with transverse bore	steel	100	29	10	M6	105,2	59,5	35,5	13	7,5	129	15,7	3	-	11,4
06500-1212046	reamed hole with slot	with transverse bore	steel	100	29	12	M6	105,2	59,5	35,5	13	7,5	129	15,7	4	-	13,8
06500-1312046	reamed hole with slot	with transverse bore	steel	125	36	12	M6	140	83	44	18,5	7,5	161	19,5	4	-	13,8
06500-1314056	reamed hole with slot	with transverse bore	steel	125	36	14	M6	140	83	44	18,5	7,5	161	19,5	5	-	16,3
06500-0110802	reamed hole with slot	without transverse hole	stainless steel	80	24	8	-	85,7	49	28,5	13	-	104	12,7	2	-	9
06500-0111003	reamed hole with slot	without transverse hole	stainless steel	80	24	10	-	85,7	49	28,5	13	-	104	12,7	3	-	11,4
06500-0121003	reamed hole with slot	without transverse hole	stainless steel	100	29	10	-	105,2	59,5	35,5	13	-	129	15,7	3	-	11,4
06500-0121204	reamed hole with slot	without transverse hole	stainless steel	100	29	12	-	105,2	59,5	35,5	13	-	129	15,7	4	-	13,8
06500-0131204	reamed hole with slot	without transverse hole	stainless steel	125	36	12	-	140	83	44	18,5	-	161	19,5	4	-	13,8
06500-0131405	reamed hole with slot	without transverse hole	stainless steel	125	36	14	-	140	83	44	18,5	-	161	19,5	5	-	16,3
06500-01108026	reamed hole with slot	with transverse bore	stainless steel	80	24	8	M6	85,7	49	28,5	13	7,5	104	12,7	2	-	9
06500-01110036	reamed hole with slot	with transverse bore	stainless steel	80	24	10	M6	85,7	49	28,5	13	7,5	104	12,7	3	-	11,4
06500-01210036	reamed hole with slot	with transverse bore	stainless steel	100	29	10	M6	105,2	59,5	35,5	13	7,5	129	15,7	3	-	11,4
06500-01212046	reamed hole with slot	with transverse bore	stainless steel	100	29	12	M6	105,2	59,5	35,5	13	7,5	129	15,7	4	-	13,8
06500-01312046	reamed hole with slot	with transverse bore	stainless steel	125	36	12	M6	140	83	44	18,5	7,5	161	19,5	4	-	13,8
06500-01314056	reamed hole with slot	with transverse bore	stainless steel	125	36	14	M6	140	83	44	18,5	7,5	161	19,5	5	-	16,3
06500-2108	square socket	without transverse hole	steel	80	24	-	-	85,7	49	28,5	13	-	104	12,7	-	8	-
06500-2110	square socket	without transverse hole	steel	80	24	-	-	85,7	49	28,5	13	-	104	12,7	-	10	-

Overview of items

Order No.	Version 1	Version 2	Component material	A	D	D2	D7	H	H1	H2	H3	H4	L	L2	B3	SW	T
06500-2210	square socket	without transverse hole	steel	100	29	-	-	105,2	59,5	35,5	13	-	129	15,7	-	10	-
06500-2212	square socket	without transverse hole	steel	100	29	-	-	105,2	59,5	35,5	13	-	129	15,7	-	12	-
06500-2312	square socket	without transverse hole	steel	125	36	-	-	140	83	44	18,5	-	161	19,5	-	12	-
06500-2314	square socket	without transverse hole	steel	125	36	-	-	140	83	44	18,5	-	161	19,5	-	14	-
06500-21086	square socket	with transverse bore	steel	80	24	-	M6	85,7	49	28,5	13	7,5	104	12,7	-	8	-
06500-21106	square socket	with transverse bore	steel	80	24	-	M6	85,7	49	28,5	13	7,5	104	12,7	-	10	-
06500-22106	square socket	with transverse bore	steel	100	29	-	M6	105,2	59,5	35,5	13	7,5	129	15,7	-	10	-
06500-22126	square socket	with transverse bore	steel	100	29	-	M6	105,2	59,5	35,5	13	7,5	129	15,7	-	12	-
06500-23126	square socket	with transverse bore	steel	125	36	-	M6	140	83	44	18,5	7,5	161	19,5	-	12	-
06500-23146	square socket	with transverse bore	steel	125	36	-	M6	140	83	44	18,5	7,5	161	19,5	-	14	-