


Item description/product images



Description

Product description:

Push button latches are used for replacing and locking fixtures or hatches quickly and easily.

Toolless clamping shortens setup times.

Material:

Housing and push button stainless steel.

Version:

Housing and push button bright.

Note:

Form A for plate thickness 3 to 10 mm.

Form B for plate thickness 3 to 27 mm.

A gap of more than 0.1 mm appears between the plates if the retaining force is exceeded.

Type of operation:

Press the latch over the clamping pin without pressing the knob. The latch is now locked.

To release, press the button and pull the latch off.

Application:

Mounting option A in combination with spacer rings, for plate thickness 3 to 10 mm.

Mounting option B for plate thickness 10 to 27 mm.

Attention:

The specified pull-out forces apply only in combination with clamping pin 03192-25.

Accessory:


Spacer rings 03192-20.

Clamping pins 03192-25.

Drawing reference:

1) plate

Drawings



Overview of items

Order No.	Form	Version 1	D	D1	D2	D3	D4	H	H1	H2	L	M	SW	T	Holding force N	Clamping force N	Shearing force kN	Pullout force F kN	Temperature resistance
03192-15-11	A	with head	6	19	32	11	-	23	15,5	8,5	9,5	M16X1	17	3	100	6	1,1	0,25	≤180 °C
03192-15-12	B	without head	6	-	19	11	20	23	19,5	-	9,5	M16X1	17	10-27	100	6	1,1	0,25	≤180 °C