


Item description/product images



Description

Material:

Steel.

Version:

Hardened and ground (HRC 60 ± 2).

Note:

The locating pins are designed to make the joining process easier. Used in combination with hardened locating bushes 02026, they enable exact, low-wear, and fast changes of the workpiece.


Versions D1 = 5 and D1 = 6 do not have an internal thread.

Drawing reference:

Form B: cylindrical pin

Form C: rhomboid pin

Drawings



Overview of items

Order No.	Form	Version 1	B	D1	D2	G	H	H1	H2	R	T
02025-205	B	Clamping Component Set	-	5	3	-	8	3	5	1,50	-
02025-206	B	Clamping Component Set	-	6	4	-	10	4	6	1,80	-
02025-208	B	Clamping Component Set	-	8	6	M2,5	11,4	6	7,4	2,5	5
02025-210	B	Clamping Component Set	-	10	7	M2,5	13,7	7	9,7	3	5
02025-212	B	Clamping Component Set	-	12	8	M3	16	8	12	3,5	6
02025-216	B	Clamping Component Set	-	16	12	M4	20	12	15	5	8
02025-220	B	Clamping Component Set	-	20	14	M5	25,5	14	19,5	6	10
02025-305	B	500 m / on the roll	-	5	3	-	10	3	5	1,50	-
02025-306	B	500 m / on the roll	-	6	4	-	12	4	6	1,80	-
02025-308	B	500 m / on the roll	-	8	6	M2,5	17,4	6	7,4	2,5	5
02025-310	B	500 m / on the roll	-	10	7	M2,5	21,7	7	9,7	3	5
02025-312	B	500 m / on the roll	-	12	8	M3	24	8	12	3,5	6
02025-316	B	500 m / on the roll	-	16	12	M4	29	12	15	5	8
02025-320	B	500 m / on the roll	-	20	14	M5	35,5	14	19,5	6	10
02025-405	C	Clamping Component Set	-	5	3	-	8	3	5	1,50	-
02025-406	C	Clamping Component Set	-	6	4	-	10	4	6	1,80	-
02025-408	C	Clamping Component Set	2,5	8	6	M2,5	11,4	6	7,4	2,5	5
02025-410	C	Clamping Component Set	3,0	10	7	M2,5	13,7	7	9,7	3	5
02025-412	C	Clamping Component Set	3,5	12	8	M3	16	8	12	3,5	6
02025-416	C	Clamping Component Set	5	16	12	M4	20	12	15	5	8
02025-420	C	Clamping Component Set	6	20	14	M5	25,5	14	19,5	6	10
02025-505	C	500 m / on the roll	-	5	3	-	10	3	5	1,50	-
02025-506	C	500 m / on the roll	-	6	4	-	12	4	6	1,80	-
02025-508	C	500 m / on the roll	2,5	8	6	M2,5	17,4	6	7,4	2,5	5
02025-510	C	500 m / on the roll	3,0	10	7	M2,5	21,7	7	9,7	3	5
02025-512	C	500 m / on the roll	3,5	12	8	M3	24	8	12	3,5	6
02025-516	C	500 m / on the roll	5	16	12	M4	29	12	15	5	8
02025-520	C	500 m / on the roll	6	20	14	M5	35,5	14	19,5	6	10

