


Item description/product images



Description

Material:

Handwheel aluminium.

Hub cover black thermoplastic.

ISO 4027 grub screw, steel grade 45 H, black.

Version:

Black or silver powder-coated.

With reamed hole.

With reamed hole and keyway.

With reamed hole and transverse bore.

With reamed hole, keyway and transverse bore.

Note:

Wheel rim radial and axial run-out ≤ 0.4 mm.

Assembly:

The hub cover is supplied unassembled.

The handwheels can be secured to a shaft using a transverse pin or by parallel key connection together with a DIN 6912 cap screw and a handwheel washer 07375.

By the versions with transverse bore, fixation is carried out using an ISO 4027 grub screw.

Supplied with:

Aluminium handwheel.

Hub cover.

ISO 4027 grub screw (type with transverse bore).

Accessory:

07375 Handwheel washers.

07161 Socket head screws with low head DIN 6912.


Drawing reference:

1) Position of the transverse bore to the keyway is offset by 90° .

Item description/product images



Drawings



Overview of items

Order No.	Main colour	Form	Form definition	D1	D2	D3	L1	L3	H	H2	D7	B3	T
06276-10-1251216	9-pin	A	precipitation hardened	125	12	31	18	36	17,6	6,5	M6	-	-

Overview of items

Order No.	Main colour	Form	Form definition	D1	D2	D3	L1	L3	H	H2	D7	B3	T
06276-10-1251416	9-pin	A	precipitation hardened	125	14	31	18	36	17,6	6,5	M6	-	-
06276-10-1601416	9-pin	A	precipitation hardened	160	14	36	20	40	19,4	6,5	M6	-	-
06276-10-1601616	9-pin	A	precipitation hardened	160	16	36	20	40	19,4	8	M6	-	-
06276-10-1251226	Bushing and fitting pieces	A	precipitation hardened	125	12	31	18	36	17,6	6,5	M6	-	-
06276-10-1251426	Bushing and fitting pieces	A	precipitation hardened	125	14	31	18	36	17,6	6,5	M6	-	-
06276-10-1601426	Bushing and fitting pieces	A	precipitation hardened	160	14	36	20	40	19,4	6,5	M6	-	-
06276-10-1601626	Bushing and fitting pieces	A	precipitation hardened	160	16	36	20	40	19,4	8	M6	-	-
06276-10-125121046	9-pin	B	Protective Insert	125	12	31	18	36	17,6	6,5	M6	4	13,8
06276-10-125141056	9-pin	B	Protective Insert	125	14	31	18	36	17,6	6,5	M6	5	16,3
06276-10-160141056	9-pin	B	Protective Insert	160	14	36	20	40	19,4	6,5	M6	5	16,3
06276-10-160161056	9-pin	B	Protective Insert	160	16	36	20	40	19,4	8	M6	5	18,3
06276-10-125122046	Bushing and fitting pieces	B	Protective Insert	125	12	31	18	36	17,6	6,5	M6	4	13,8
06276-10-125142056	Bushing and fitting pieces	B	Protective Insert	125	14	31	18	36	17,6	6,5	M6	5	16,3
06276-10-160142056	Bushing and fitting pieces	B	Protective Insert	160	14	36	20	40	19,4	6,5	M6	5	16,3
06276-10-160162056	Bushing and fitting pieces	B	Protective Insert	160	16	36	20	40	19,4	8	M6	5	18,3
06276-10-12512104	9-pin	C	1 kg can	125	12	31	18	36	17,6	-	-	4	13,8
06276-10-12514105	9-pin	C	1 kg can	125	14	31	18	36	17,6	-	-	5	16,3
06276-10-16014105	9-pin	C	1 kg can	160	14	36	20	40	19,4	-	-	5	16,3
06276-10-16016105	9-pin	C	1 kg can	160	16	36	20	40	19,4	-	-	5	18,3
06276-10-12512204	Bushing and fitting pieces	C	1 kg can	125	12	31	18	36	17,6	-	-	4	13,8
06276-10-12514205	Bushing and fitting pieces	C	1 kg can	125	14	31	18	36	17,6	-	-	5	16,3
06276-10-16014205	Bushing and fitting pieces	C	1 kg can	160	14	36	20	40	19,4	-	-	5	16,3
06276-10-16016205	Bushing and fitting pieces	C	1 kg can	160	16	36	20	40	19,4	-	-	5	18,3
06276-10-125121	9-pin	E	Positioning table with fine adjustment	125	12	31	18	36	17,6	-	-	-	-
06276-10-125141	9-pin	E	Positioning table with fine adjustment	125	14	31	18	36	17,6	-	-	-	-
06276-10-160141	9-pin	E	Positioning table with fine adjustment	160	14	36	20	40	19,4	-	-	-	-
06276-10-160161	9-pin	E	Positioning table with fine adjustment	160	16	36	20	40	19,4	-	-	-	-
06276-10-125122	Bushing and fitting pieces	E	Positioning table with fine adjustment	125	12	31	18	36	17,6	-	-	-	-
06276-10-125142	Bushing and fitting pieces	E	Positioning table with fine adjustment	125	14	31	18	36	17,6	-	-	-	-
06276-10-160142	Bushing and fitting pieces	E	Positioning table with fine adjustment	160	14	36	20	40	19,4	-	-	-	-
06276-10-160162	Bushing and fitting pieces	E	Positioning table with fine adjustment	160	16	36	20	40	19,4	-	-	-	-