

Item description/product images



Description

Material:

Steel.

Version:

Thrust pin steel, hardened and electro zinc-plated.

Sleeve blue electro zinc-plated.

Note:


Lateral spring plungers with threaded sleeve can be individually adjusted to suit the the part being held. The threaded sleeve is also suitable for screwing into thin sheet metal as it can be fastened with one or two nuts.

W and Z are customer specified.

Drawing reference:

1) assembly tool

Drawings



Overview of items

Order No.	Component material	L	L1	D	D1	±S	F ca.N	X	SW	K	Order No. assembly tool
03334-1020X12	steel	11,5	6,7	M12	5	0,8	20	1,6	10	2x60°	03334-06

Overview of items

Order No.	Component material	L	L1	D	D1	±S	F ca.N	X	SW	K	Order No. assembly tool
03334-1020X20	steel	19	6,7	M12	5	0,8	20	1,6	10	2x60°	03334-06
03334-1020X27	steel	26,5	6,7	M12	5	0,8	20	1,6	10	2x60°	03334-06
03334-1050X12	steel	11,5	6,7	M12	5	0,8	50	1,6	10	2x60°	03334-06
03334-1050X20	steel	19	6,7	M12	5	0,8	50	1,6	10	2x60°	03334-06
03334-1050X27	steel	26,5	6,7	M12	5	0,8	50	1,6	10	2x60°	03334-06
03334-1100X12	steel	11,5	6,7	M12	5	0,8	100	1,6	10	2x60°	03334-06
03334-1100X20	steel	19	6,7	M12	5	0,8	100	1,6	10	2x60°	03334-06
03334-1100X27	steel	26,5	6,7	M12	5	0,8	100	1,6	10	2x60°	03334-06
03334-1040X12	steel	11,5	10,7	M12	6	1	40	1,8	10	2x60°	03334-06
03334-1040X20	steel	19	10,7	M12	6	1	40	1,8	10	2x60°	03334-06
03334-1040X27	steel	26,5	10,7	M12	6	1	40	1,8	10	2x60°	03334-06
03334-1075X12	steel	11,5	10,7	M12	6	1	75	1,8	10	2x60°	03334-06
03334-1075X20	steel	19	10,7	M12	6	1	75	1,8	10	2x60°	03334-06
03334-1075X27	steel	26,5	10,7	M12	6	1	75	1,8	10	2x60°	03334-06
03334-1150X12	steel	11,5	10,7	M12	6	1	100	1,8	10	2x60°	03334-06
03334-1150X20	steel	19	10,7	M12	6	1	100	1,8	10	2x60°	03334-06
03334-1150X27	steel	26,5	10,7	M12	6	1	100	1,8	10	2x60°	03334-06
03334-1100X16	steel	18	16,7	M18X1,5	10	1,6	100	3,2	16	2,5x60°	03334-10
03334-1100X29	steel	31,5	16,7	M18X1,5	10	1,6	100	3,2	16	2,5x60°	03334-10
03334-1100X43	steel	45	16,7	M18X1,5	10	1,6	100	3,2	16	2,5x60°	03334-10
03334-1200X16	steel	18	16,7	M18X1,5	10	1,6	150	3,2	16	2,5x60°	03334-10
03334-1200X29	steel	31,5	16,7	M18X1,5	10	1,6	150	3,2	16	2,5x60°	03334-10
03334-1200X43	steel	45	16,7	M18X1,5	10	1,6	150	3,2	16	2,5x60°	03334-10
03334-1300X16	steel	18	16,7	M18X1,5	10	1,6	200	3,2	16	2,5x60°	03334-10
03334-1300X29	steel	31,5	16,7	M18X1,5	10	1,6	200	3,2	16	2,5x60°	03334-10
03334-1300X43	steel	45	16,7	M18X1,5	10	1,6	200	3,2	16	2,5x60°	03334-10