

Item description/product images

**Description****Material:**

EN-GJL-250

Version:

Bright, ground.

Note:

These precise slideways are used in e.g. machine, fixture and metrology equipment construction as well as in the optical and precision engineering industries. The central set screw M1 can be replaced by a clamping lever 06460.

The stated permissible load values (F) are designed for dynamic loads with a service life of 1 million travel cycles.

For static loads, 10 times the table value F is permitted.

The torque values apply only to centred slides.

An additional centring hole is located at holes D2 and D3 on the top of the slide. Other connecting elements can be precisely mounted on the slide in combination with our centring rings 20240.


TI E = number of fastening holes E/M inside.

TA E = number of fastening holes E/M outside.

TI E1 = number of fastening holes E1/D1 inside.

TA E1 = number of fastening holes E1/D1 outside.

Drawings



Overview of items

Order No.	A	A1	A2	B	B1	C	D1	D2	D3	D4	E	E1	E2	E3	TI E	TA E	TI E1	TA E1
21060-050080	25	15	17,5	50	49,5	15	7	M4	4,3	8,2	-	14	28	28	-	-	10	6
21060-050105	25	15	17,5	50	49,5	20	7	M4	4,3	8,2	-	14	28	28	-	-	14	8
21060-050130	25	15	17,5	50	49,5	25	7	M4	4,3	8,2	-	28	28	28	-	-	10	10
21060-075105	32	19,5	22	75	74,5	20	10	M5	5,3	10	62	25	25	50	4	4	6	6
21060-075130	32	19,5	22	75	74,5	25	10	M5	5,3	10	62	25	25	50	4	4	10	10
21060-100110	40	24	28	100	99,5	20	10	M5	5,3	10,2	86	25	25	50	4	4	6	6
21060-100135	40	24	28	100	99,5	25	10	M5	5,3	10,2	86	50	50	50	4	4	6	6
21060-100160	40	24	28	100	99,5	30	10	M5	5,3	10,2	86	50	50	50	4	4	6	6

Overview of items

Order No.	L	L2	L3	P	P1	M	M1	M2	T1	T2	F N	Mx Nm	My Nm	Mz Nm
21060-050080	80	40	5,5	1,6	3,2	-	M5	M4	0,02	0,02	75	4	6	5
21060-050105	105	40	5,5	1,6	3,2	-	M5	M4	0,02	0,02	90	7	7	8
21060-050130	130	40	5,5	1,6	3,2	-	M5	M4	0,025	0,025	120	10	9	12
21060-075105	105	60	5,5	2,1	3,6	M5	M5	M5	0,02	0,02	130	9	15	10
21060-075130	130	60	5,5	2,1	3,6	M5	M5	M5	0,025	0,025	160	15	18	15
21060-100110	110	-	-	2,1	3,8	M6	M6	-	0,02	0,02	155	11	26	12
21060-100135	135	88	8	2,1	3,8	M6	M6	M6	0,025	0,025	190	17	32	19
21060-100160	160	88	8	2,1	3,8	M6	M6	M6	0,025	0,025	230	24	37	26