


Item description/product images



Description

Material:

Handwheel body thermoplastic.

Hub steel, strength class 5.8, or stainless steel 1.4404.

Version:

Thermoplastic black grey.

Steel parts black oxidised.

Stainless steel bright.


Note:

The hub cover is supplied unassembled.

The handwheels can be secured to a shaft using a transverse pin or by parallel key connection together with a DIN 6912 cap screw and a DIN 7349 washer.


Versions with transverse bore are secured using the ISO 4027 (DIN 914) grub screw.

Drawings



Drawings

DIN 6885-1



Overview of items

Order No.	Version 1	Version 2	Component material	D	D1	D2	D3	D7	A1	H	H2	L1	L3	B3	T
06262-108008	reamed hole	without transverse hole	steel	25	80	8H7	19	-	2,5	17,5	-	13	37,5	-	-
06262-108010	reamed hole	without transverse hole	steel	25	80	10H7	19	-	2,5	17,5	-	13	37,5	-	-
06262-108012	reamed hole	without transverse hole	steel	25	80	12H7	19	-	2,5	17,5	-	13	37,5	-	-
06262-210010	reamed hole	without transverse hole	steel	28	100	10H7	19	-	3	20	-	13	44	-	-
06262-210012	reamed hole	without transverse hole	steel	28	100	12H7	19	-	3	20	-	13	44	-	-
06262-312512	reamed hole	without transverse hole	steel	35	125	12H7	25	-	4	23,5	-	18,5	53	-	-
06262-312514	reamed hole	without transverse hole	steel	35	125	14H7	25	-	4	23,5	-	18,5	53	-	-
06262-312516	reamed hole	without transverse hole	steel	35	125	16H7	25	-	4	23,5	-	18,5	53	-	-
06262-416014	reamed hole	without transverse hole	steel	45	160	14H7	25	-	5,6	28	-	18,5	64,5	-	-
06262-416016	reamed hole	without transverse hole	steel	45	160	16H7	25	-	5,6	28	-	18,5	64,5	-	-
06262-10800802	reamed hole with slot	without transverse hole	steel	25	80	8H7	19	-	2,5	17,5	-	13	37,5	2	9
06262-10801003	reamed hole with slot	without transverse hole	steel	25	80	10H7	19	-	2,5	17,5	-	13	37,5	3	11,4
06262-10801204	reamed hole with slot	without transverse hole	steel	25	80	12H7	19	-	2,5	17,5	-	13	37,5	4	13,8
06262-21001003	reamed hole with slot	without transverse hole	steel	28	100	10H7	19	-	3	20	-	13	44	3	11,4
06262-21001204	reamed hole with slot	without transverse hole	steel	28	100	12H7	19	-	3	20	-	13	44	4	13,8
06262-31251204	reamed hole with slot	without transverse hole	steel	35	125	12H7	25	-	4	23,5	-	18,5	53	4	13,8
06262-31251405	reamed hole with slot	without transverse hole	steel	35	125	14H7	25	-	4	23,5	-	18,5	53	5	16,3
06262-31251605	reamed hole with slot	without transverse hole	steel	35	125	16H7	25	-	4	23,5	-	18,5	53	5	18,3
06262-41601405	reamed hole with slot	without transverse hole	steel	45	160	14H7	25	-	5,6	28	-	18,5	64,5	5	16,3
06262-41601605	reamed hole with slot	without transverse hole	steel	45	160	16H7	25	-	5,6	28	-	18,5	64,5	5	18,3
06262-1080086	reamed hole	with transverse bore	steel	25	80	8H7	19	M6	2,5	17,5	7,5	13	37,5	-	-
06262-1080106	reamed hole	with transverse bore	steel	25	80	10H7	19	M6	2,5	17,5	7,5	13	37,5	-	-
06262-1080126	reamed hole	with transverse bore	steel	25	80	12H7	19	M6	2,5	17,5	7,5	13	37,5	-	-
06262-2100106	reamed hole	with transverse bore	steel	28	100	10H7	19	M6	3	20	7,5	13	44	-	-
06262-2100126	reamed hole	with transverse bore	steel	28	100	12H7	19	M6	3	20	7,5	13	44	-	-
06262-3125126	reamed hole	with transverse bore	steel	35	125	12H7	25	M6	4	23,5	7,5	18,5	53	-	-
06262-3125146	reamed hole	with transverse bore	steel	35	125	14H7	25	M6	4	23,5	7,5	18,5	53	-	-
06262-3125166	reamed hole	with transverse bore	steel	35	125	16H7	25	M6	4	23,5	7,5	18,5	53	-	-
06262-4160146	reamed hole	with transverse bore	steel	45	160	14H7	25	M6	5,6	28	7,5	18,5	64,5	-	-
06262-4160166	reamed hole	with transverse bore	steel	45	160	16H7	25	M6	5,6	28	7,5	18,5	64,5	-	-
06262-108008026	reamed hole with slot	with transverse bore	steel	25	80	8H7	19	M6	2,5	17,5	7,5	13	37,5	2	9
06262-108010036	reamed hole with slot	with transverse bore	steel	25	80	10H7	19	M6	2,5	17,5	7,5	13	37,5	3	11,4
06262-108012046	reamed hole with slot	with transverse bore	steel	25	80	12H7	19	M6	2,5	17,5	7,5	13	37,5	4	13,8
06262-210010036	reamed hole with slot	with transverse bore	steel	28	100	10H7	19	M6	3	20	7,5	13	44	3	11,4
06262-210012046	reamed hole with slot	with transverse bore	steel	28	100	12H7	19	M6	3	20	7,5	13	44	4	13,8
06262-312512046	reamed hole with slot	with transverse bore	steel	35	125	12H7	25	M6	4	23,5	7,5	18,5	53	4	13,8
06262-312514056	reamed hole with slot	with transverse bore	steel	35	125	14H7	25	M6	4	23,5	7,5	18,5	53	5	16,3
06262-312516056	reamed hole with slot	with transverse bore	steel	35	125	16H7	25	M6	4	23,5	7,5	18,5	53	5	18,3
06262-416014056	reamed hole with slot	with transverse bore	steel	45	160	14H7	25	M6	5,6	28	7,5	18,5	64,5	5	16,3
06262-416016056	reamed hole with slot	with transverse bore	steel	45	160	16H7	25	M6	5,6	28	7,5	18,5	64,5	5	18,3
06262-0108008	reamed hole	without transverse hole	stainless steel	25	80	8H7	19	-	2,5	17,5	-	13	37,5	-	-
06262-0108010	reamed hole	without transverse hole	stainless steel	25	80	10H7	19	-	2,5	17,5	-	13	37,5	-	-
06262-0108012	reamed hole	without transverse hole	stainless steel	25	80	12H7	19	-	2,5	17,5	-	13	37,5	-	-
06262-0210010	reamed hole	without transverse hole	stainless steel	28	100	10H7	19	-	3	20	-	13	44	-	-
06262-0210012	reamed hole	without transverse hole	stainless steel	28	100	12H7	19	-	3	20	-	13	44	-	-
06262-0312512	reamed hole	without transverse hole	stainless steel	35	125	12H7	25	-	4	23,5	-	18,5	53	-	-
06262-0312514	reamed hole	without transverse hole	stainless steel	35	125	14H7	25	-	4	23,5	-	18,5	53	-	-
06262-0312516	reamed hole	without transverse hole	stainless steel	35	125	16H7	25	-	4	23,5	-	18,5	53	-	-
06262-0416014	reamed hole	without transverse hole	stainless steel	45	160	14H7	25	-	5,6	28	-	18,5	64,5	-	-
06262-0416016	reamed hole	without transverse hole	stainless steel	45	160	16H7	25	-	5,6	28	-	18,5	64,5	-	-

Overview of items

Order No.	Version 1	Version 2	Component material	D	D1	D2	D3	D7	A1	H	H2	L1	L3	B3	T
06262-010800802	reamed hole with slot	without transverse hole	stainless steel	25	80	8H7	19	-	2,5	17,5	-	13	37,5	2	9
06262-010801003	reamed hole with slot	without transverse hole	stainless steel	25	80	10H7	19	-	2,5	17,5	-	13	37,5	3	11,4
06262-010801204	reamed hole with slot	without transverse hole	stainless steel	25	80	12H7	19	-	2,5	17,5	-	13	37,5	4	13,8
06262-021001003	reamed hole with slot	without transverse hole	stainless steel	28	100	10H7	19	-	3	20	-	13	44	3	11,4
06262-021001204	reamed hole with slot	without transverse hole	stainless steel	28	100	12H7	19	-	3	20	-	13	44	4	13,8
06262-031251204	reamed hole with slot	without transverse hole	stainless steel	35	125	12H7	25	-	4	23,5	-	18,5	53	4	13,8
06262-031251405	reamed hole with slot	without transverse hole	stainless steel	35	125	14H7	25	-	4	23,5	-	18,5	53	5	16,3
06262-031251605	reamed hole with slot	without transverse hole	stainless steel	35	125	16H7	25	-	4	23,5	-	18,5	53	5	18,3
06262-041601405	reamed hole with slot	without transverse hole	stainless steel	45	160	14H7	25	-	5,6	28	-	18,5	64,5	5	16,3
06262-041601605	reamed hole with slot	without transverse hole	stainless steel	45	160	16H7	25	-	5,6	28	-	18,5	64,5	5	18,3
06262-010800806	reamed hole	with transverse bore	stainless steel	25	80	8H7	19	M6	2,5	17,5	7,5	13	37,5	-	-
06262-010801006	reamed hole	with transverse bore	stainless steel	25	80	10H7	19	M6	2,5	17,5	7,5	13	37,5	-	-
06262-010801206	reamed hole	with transverse bore	stainless steel	25	80	12H7	19	M6	2,5	17,5	7,5	13	37,5	-	-
06262-021001006	reamed hole	with transverse bore	stainless steel	28	100	10H7	19	M6	3	20	7,5	13	44	-	-
06262-021001206	reamed hole	with transverse bore	stainless steel	28	100	12H7	19	M6	3	20	7,5	13	44	-	-
06262-031251206	reamed hole	with transverse bore	stainless steel	35	125	12H7	25	M6	4	23,5	7,5	18,5	53	-	-
06262-031251406	reamed hole	with transverse bore	stainless steel	35	125	14H7	25	M6	4	23,5	7,5	18,5	53	-	-
06262-031251606	reamed hole	with transverse bore	stainless steel	35	125	16H7	25	M6	4	23,5	7,5	18,5	53	-	-
06262-041601406	reamed hole	with transverse bore	stainless steel	45	160	14H7	25	M6	5,6	28	7,5	18,5	64,5	-	-
06262-041601606	reamed hole	with transverse bore	stainless steel	45	160	16H7	25	M6	5,6	28	7,5	18,5	64,5	-	-
06262-0108008026	reamed hole with slot	with transverse bore	stainless steel	25	80	8H7	19	M6	2,5	17,5	7,5	13	37,5	2	9
06262-0108010036	reamed hole with slot	with transverse bore	stainless steel	25	80	10H7	19	M6	2,5	17,5	7,5	13	37,5	3	11,4
06262-0108012046	reamed hole with slot	with transverse bore	stainless steel	25	80	12H7	19	M6	2,5	17,5	7,5	13	37,5	4	13,8
06262-0210010036	reamed hole with slot	with transverse bore	stainless steel	28	100	10H7	19	M6	3	20	7,5	13	44	3	11,4
06262-0210012046	reamed hole with slot	with transverse bore	stainless steel	28	100	12H7	19	M6	3	20	7,5	13	44	4	13,8
06262-0312512046	reamed hole with slot	with transverse bore	stainless steel	35	125	12H7	25	M6	4	23,5	7,5	18,5	53	4	13,8
06262-0312514056	reamed hole with slot	with transverse bore	stainless steel	35	125	14H7	25	M6	4	23,5	7,5	18,5	53	5	16,3
06262-0312516056	reamed hole with slot	with transverse bore	stainless steel	35	125	16H7	25	M6	4	23,5	7,5	18,5	53	5	18,3
06262-0416014056	reamed hole with slot	with transverse bore	stainless steel	45	160	14H7	25	M6	5,6	28	7,5	18,5	64,5	5	16,3
06262-0416016056	reamed hole with slot	with transverse bore	stainless steel	45	160	16H7	25	M6	5,6	28	7,5	18,5	64,5	5	18,3