

Item description/product images



Description

Material:

Steel grade 5.8.

Version:

Black oxidised.

Pin hardened and ground.


Note:

Cam-action indexing plungers are used when the indexing pin should not project all the time. Turning the handle through 180° retracts the pin.

A notch ensures that the handle remains in this position.

A stop prevents the handle being rotated through more than 180° ensuring that the pin remains retracted.

Selecting which side the stop is on defines the rotation direction of the plunger.

**Drawing reference:**

Form A: grip uncoated without nut

Form C: grip powder-coated without nut


Form B: grip uncoated with nut

Form D: grip powder-coated with nut

1) stop left

2) stop right

Drawings



Overview of items

Order No.	Form	Version 2	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
03099-20-1040410	A	0,29	4	M10	10	38	25	15	9	3	6	10	-	1	8	14
03099-20-1040510	A	0,29	5	M10	10	38	25	15	9	3	6	10	-	1,3	8	14
03099-20-1040610	A	0,29	6	M10	10	38	25	15	9	3	6	10	-	1,8	8	14
03099-20-1040512	A	0,29	5	M12	12	47,8	30	19	10,8	3,6	8	12	-	1,3	8	15
03099-20-1040612	A	0,29	6	M12	12	47,8	30	19	10,8	3,6	8	12	-	1,8	8	15
03099-20-1040812	A	0,29	8	M12	12	47,8	30	19	10,8	3,6	8	12	-	2,3	8	15
03099-20-1040616	A	0,29	6	M16	16	60,4	40	26	14,4	4,8	10	16	-	1,8	15	35
03099-20-1040816	A	0,29	8	M16	16	60,4	40	26	14,4	4,8	10	16	-	2,3	15	35
03099-20-1041016	A	0,29	10	M16	16	60,4	40	26	14,4	4,8	10	16	-	2,8	15	35
03099-20-10408201	A	0,29	8	M20x1,5	20	70	50	30	18	6	12	20	-	2,3	20	60
03099-20-10410201	A	0,29	10	M20x1,5	20	70	50	30	18	6	12	20	-	2,8	20	60
03099-20-10412201	A	0,29	12	M20x1,5	20	70	50	30	18	6	12	20	-	3	20	60
03099-20-2040410	A	0,32	4	M10	10	38	25	15	9	3	6	10	-	1	8	14
03099-20-2040510	A	0,32	5	M10	10	38	25	15	9	3	6	10	-	1,3	8	14
03099-20-2040610	A	0,32	6	M10	10	38	25	15	9	3	6	10	-	1,8	8	14
03099-20-2040512	A	0,32	5	M12	12	47,8	30	19	10,8	3,6	8	12	-	1,3	8	15
03099-20-2040612	A	0,32	6	M12	12	47,8	30	19	10,8	3,6	8	12	-	1,8	8	15
03099-20-2040812	A	0,32	8	M12	12	47,8	30	19	10,8	3,6	8	12	-	2,3	8	15
03099-20-2040616	A	0,32	6	M16	16	60,4	40	26	14,4	4,8	10	16	-	1,8	15	35
03099-20-2040816	A	0,32	8	M16	16	60,4	40	26	14,4	4,8	10	16	-	2,3	15	35
03099-20-2041016	A	0,32	10	M16	16	60,4	40	26	14,4	4,8	10	16	-	2,8	15	35
03099-20-20408201	A	0,32	8	M20x1,5	20	70	50	30	18	6	12	20	-	2,3	20	60
03099-20-20410201	A	0,32	10	M20x1,5	20	70	50	30	18	6	12	20	-	2,8	20	60
03099-20-20412201	A	0,32	12	M20x1,5	20	70	50	30	18	6	12	20	-	3	20	60
03099-20-1050410	B	0,29	4	M10	10	38	25	15	9	3	6	10	17	1	8	14
03099-20-1050510	B	0,29	5	M10	10	38	25	15	9	3	6	10	17	1,3	8	14
03099-20-1050610	B	0,29	6	M10	10	38	25	15	9	3	6	10	17	1,8	8	14
03099-20-1050512	B	0,29	5	M12	12	47,8	30	19	10,8	3,6	8	12	19	1,3	8	15
03099-20-1050612	B	0,29	6	M12	12	47,8	30	19	10,8	3,6	8	12	19	1,8	8	15
03099-20-1050812	B	0,29	8	M12	12	47,8	30	19	10,8	3,6	8	12	19	2,3	8	15
03099-20-1050616	B	0,29	6	M16	16	60,4	40	26	14,4	4,8	10	16	24	1,8	15	35
03099-20-1050816	B	0,29	8	M16	16	60,4	40	26	14,4	4,8	10	16	24	2,3	15	35
03099-20-1051016	B	0,29	10	M16	16	60,4	40	26	14,4	4,8	10	16	24	2,8	15	35
03099-20-10508201	B	0,29	8	M20x1,5	20	70	50	30	18	6	12	20	30	2,3	20	60
03099-20-10510201	B	0,29	10	M20x1,5	20	70	50	30	18	6	12	20	30	2,8	20	60
03099-20-10512201	B	0,29	12	M20x1,5	20	70	50	30	18	6	12	20	30	3	20	60
03099-20-2050410	B	0,32	4	M10	10	38	25	15	9	3	6	10	17	1	8	14
03099-20-2050510	B	0,32	5	M10	10	38	25	15	9	3	6	10	17	1,3	8	14
03099-20-2050610	B	0,32	6	M10	10	38	25	15	9	3	6	10	17	1,8	8	14
03099-20-2050512	B	0,32	5	M12	12	47,8	30	19	10,8	3,6	8	12	19	1,3	8	15
03099-20-2050612	B	0,32	6	M12	12	47,8	30	19	10,8	3,6	8	12	19	1,8	8	15
03099-20-2050812	B	0,32	8	M12	12	47,8	30	19	10,8	3,6	8	12	19	2,3	8	15
03099-20-2050616	B	0,32	6	M16	16	60,4	40	26	14,4	4,8	10	16	24	1,8	15	35
03099-20-2050816	B	0,32	8	M16	16	60,4	40	26	14,4	4,8	10	16	24	2,3	15	35
03099-20-2051016	B	0,32	10	M16	16	60,4	40	26	14,4	4,8	10	16	24	2,8	15	35
03099-20-20508201	B	0,32	8	M20x1,5	20	70	50	30	18	6	12	20	30	2,3	20	60
03099-20-20510201	B	0,32	10	M20x1,5	20	70	50	30	18	6	12	20	30	2,8	20	60
03099-20-20512201	B	0,32	12	M20x1,5	20	70	50	30	18	6	12	20	30	3	20	60
03099-20-1060410	C	0,29	4	M10	10	38	25	15	9	3	6	10	-	1	8	14
03099-20-1060510	C	0,29	5	M10	10	38	25	15	9	3	6	10	-	1,3	8	14
03099-20-1060610	C	0,29	6	M10	10	38	25	15	9	3	6	10	-	1,8	8	14
03099-20-1060512	C	0,29	5	M12	12	47,8	30	19	10,8	3,6	8	12	-	1,3	8	15
03099-20-1060612	C	0,29	6	M12	12	47,8	30	19	10,8	3,6	8	12	-	1,8	8	15
03099-20-1060812	C	0,29	8	M12	12	47,8	30	19	10,8	3,6	8	12	-	2,3	8	15
03099-20-1060616	C	0,29	6	M16	16	60,4	40	26	14,4	4,8	10	16	-	1,8	15	35
03099-20-1060816	C	0,29	8	M16	16	60,4	40	26	14,4	4,8	10	16	-	2,3	15	35
03099-20-1061016	C	0,29	10	M16	16	60,4	40	26	14,4	4,8	10	16	-	2,8	15	35
03099-20-10608201	C	0,29	8	M20x1,5	20	70	50	30	18	6	12	20	-	2,3	20	60
03099-20-10610201	C	0,29	10	M20x1,5	20	70	50	30	18	6	12	20	-	2,8	20	60
03099-20-10612201	C	0,29	12	M20x1,5	20	70	50	30	18	6	12	20	-	3	20	60
03099-20-2060410	C	0,32	4	M10	10	38	25	15	9	3	6	10	-	1	8	14
03099-20-2060510	C	0,32	5	M10	10	38	25	15	9	3	6	10	-	1,3	8	14
03099-20-2060610	C	0,32	6	M10	10	38	25	15	9	3	6	10	-	1,8	8	14
03099-20-2060512	C	0,32	5	M12	12	47,8	30	19	10,8	3,6	8	12	-	1,3	8	15

Overview of items

Order No.	Form	Version 2	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
03099-20-2060612	C	0,32	6	M12	12	47,8	30	19	10,8	3,6	8	12	-	1,8	8	15
03099-20-2060812	C	0,32	8	M12	12	47,8	30	19	10,8	3,6	8	12	-	2,3	8	15
03099-20-2060616	C	0,32	6	M16	16	60,4	40	26	14,4	4,8	10	16	-	1,8	15	35
03099-20-2060816	C	0,32	8	M16	16	60,4	40	26	14,4	4,8	10	16	-	2,3	15	35
03099-20-2061016	C	0,32	10	M16	16	60,4	40	26	14,4	4,8	10	16	-	2,8	15	35
03099-20-20608201	C	0,32	8	M20x1,5	20	70	50	30	18	6	12	20	-	2,3	20	60
03099-20-20610201	C	0,32	10	M20x1,5	20	70	50	30	18	6	12	20	-	2,8	20	60
03099-20-20612201	C	0,32	12	M20x1,5	20	70	50	30	18	6	12	20	-	3	20	60
03099-20-1070410	D	0,29	4	M10	10	38	25	15	9	3	6	10	17	1	8	14
03099-20-1070510	D	0,29	5	M10	10	38	25	15	9	3	6	10	17	1,3	8	14
03099-20-1070610	D	0,29	6	M10	10	38	25	15	9	3	6	10	17	1,8	8	14
03099-20-1070512	D	0,29	5	M12	12	47,8	30	19	10,8	3,6	8	12	19	1,3	8	15
03099-20-1070612	D	0,29	6	M12	12	47,8	30	19	10,8	3,6	8	12	19	1,8	8	15
03099-20-1070812	D	0,29	8	M12	12	47,8	30	19	10,8	3,6	8	12	19	2,3	8	15
03099-20-1070616	D	0,29	6	M16	16	60,4	40	26	14,4	4,8	10	16	24	1,8	15	35
03099-20-1070816	D	0,29	8	M16	16	60,4	40	26	14,4	4,8	10	16	24	2,3	15	35
03099-20-1071016	D	0,29	10	M16	16	60,4	40	26	14,4	4,8	10	16	24	2,8	15	35
03099-20-10708201	D	0,29	8	M20x1,5	20	70	50	30	18	6	12	20	30	2,3	20	60
03099-20-10710201	D	0,29	10	M20x1,5	20	70	50	30	18	6	12	20	30	2,8	20	60
03099-20-10712201	D	0,29	12	M20x1,5	20	70	50	30	18	6	12	20	30	3	20	60
03099-20-2070410	D	0,32	4	M10	10	38	25	15	9	3	6	10	17	1	8	14
03099-20-2070510	D	0,32	5	M10	10	38	25	15	9	3	6	10	17	1,3	8	14
03099-20-2070610	D	0,32	6	M10	10	38	25	15	9	3	6	10	17	1,8	8	14
03099-20-2070512	D	0,32	5	M12	12	47,8	30	19	10,8	3,6	8	12	19	1,3	8	15
03099-20-2070612	D	0,32	6	M12	12	47,8	30	19	10,8	3,6	8	12	19	1,8	8	15
03099-20-2070812	D	0,32	8	M12	12	47,8	30	19	10,8	3,6	8	12	19	2,3	8	15
03099-20-2070616	D	0,32	6	M16	16	60,4	40	26	14,4	4,8	10	16	24	1,8	15	35
03099-20-2070816	D	0,32	8	M16	16	60,4	40	26	14,4	4,8	10	16	24	2,3	15	35
03099-20-2071016	D	0,32	10	M16	16	60,4	40	26	14,4	4,8	10	16	24	2,8	15	35
03099-20-20708201	D	0,32	8	M20x1,5	20	70	50	30	18	6	12	20	30	2,3	20	60
03099-20-20710201	D	0,32	10	M20x1,5	20	70	50	30	18	6	12	20	30	2,8	20	60
03099-20-20712201	D	0,32	12	M20x1,5	20	70	50	30	18	6	12	20	30	3	20	60