

Item description/product images



Description

Material:

Crank stainless steel 1.4308.

Cylindrical grip thermoplastic and stainless steel 1.4404.

Version:

Crank bright.

Thermoplastic black grey.


Stainless steel bright.

Note:

Similar to DIN 469.

Versions with transverse bore are secured using the ISO 4027 (DIN 914) grub screw.

Drawings



Overview of items

Order No.	Version 1	Version 2	A	D	D2	D3	D7	H	H1	H2	H3	H4	L	SW
06507-1110	reamed hole	without transverse hole	80	24	10	16	-	89	49	22	13,4	-	100	-
06507-1212	reamed hole	without transverse hole	100	28	12	20	-	108	59,5	26	16	-	124	-
06507-1314	reamed hole	without transverse hole	125	30	14	26	-	140	83	28	15,8	-	153	-
06507-1417	reamed hole	without transverse hole	160	34	17	26	-	144	83	32	19,6	-	190	-
06507-11106	reamed hole	with transverse bore	80	24	10	16	M6	89	49	22	13,4	7,5	100	-
06507-12126	reamed hole	with transverse bore	100	28	12	20	M6	108	59,5	26	16	7,5	124	-
06507-13146	reamed hole	with transverse bore	125	30	14	26	M6	140	83	28	15,8	7,5	153	-
06507-14176	reamed hole	with transverse bore	160	34	17	26	M6	144	83	32	19,6	7,5	190	-
06507-2110	square socket	without transverse hole	80	24	-	16	-	89	49	22	13,4	-	100	10
06507-2212	square socket	without transverse hole	100	28	-	20	-	108	59,5	26	16	-	124	12
06507-2314	square socket	without transverse hole	125	30	-	26	-	140	83	28	15,8	-	153	14
06507-2417	square socket	without transverse hole	160	34	-	26	-	144	83	32	19,6	-	190	17
06507-21106	square socket	with transverse bore	80	24	-	16	M6	89	49	22	13,4	7,5	100	10
06507-22126	square socket	with transverse bore	100	28	-	20	M6	108	59,5	26	16	7,5	124	12
06507-23146	square socket	with transverse bore	125	30	-	26	M6	140	83	28	15,8	7,5	153	14
06507-24176	square socket	with transverse bore	160	34	-	26	M6	144	83	32	19,6	7,5	190	17

