

Item description/product images



**Description**

**Material:**  
Swivel grips plastic.

**Note:**  
The plastic swivel grip is an innovative and ergonomic solution that has been specially developed for mounting on switch cabinets and control systems. With their robust design and high-quality materials, these swivel grips offer both functionality and durability.

The installation holes are spaced at the market standard of 50x50x50.

The swivel grips can be combined with other products for switch cabinet construction to form a 1, 2 or 3 point locking system (see technical information).


By Form A the profile half-cylinder locks are already installed into the swivel grip.

By Form B the profile half-cylinder locks for swivel grips (05601) must be ordered separately.

- Accessory:**
- 05601 Profile half-cylinder lock for swivel grips
  - 05569 Steel tongue for quarter-turn locks.
  - 05570 Steel tongue for quarter-turn locks.
  - 05601-05 Adapter for round rods, steel, stainless steel or zinc.
  - 05601-11 Zinc bushes for tongues.
  - 05601-12 Steel round rods for swivel grip.
  - 05601-13 Plastic guide for round rods.
  - 05601-20 Zinc attachment for round rods.
  - 05601-14 Plastic stop for round rods.
  - 05601-22 Plastic or zinc bar lock for flat bars.
  - 05601-21 Steel flat bars for swivel grip.
  - 05601-10 Plastic or zinc adapter for tongues.

**Drawing reference:**  
1) Mounting holes

Drawings



Overview of items

Order No.	Form	Form definition	Version 1	B	B1	H	H1	H2	L	L2
05600-02-000	A	with profile cylinder lock	single-key system	34	25	24	21	2	168	50
05600-02-100	A	with profile cylinder lock	individual keys	34	25	24	21	2	168	50

## Overview of items

Order No.	Form	Form definition	Version 1	B	B1	H	H1	H2	L	L2
05600-02-110	A	with profile cylinder lock	individual keys	34	25	24	21	2	168	50
05600-02-010	A	with profile cylinder lock	single-key system	34	25	24	21	2	168	50
05600-02-11	B	without profile cylinder lock	-	34	25	31	45	-	168	50
05600-02-01	B	without profile cylinder lock	-	34	25	31	45	-	168	50