


Item description/product images



Description

Material:

Housing aluminium

Version:

Housing bright.

Note:

Ready to install linear housing units consisting of an extruded aluminium housing with a self-aligning linear ball bearing 21510 and seals both sides. The bearings are secured in the housing with DIN 472 circlips.

Recommended shaft tolerance: h6.

Load ratings according to the linear ball bearing specifications.

On request:

Linear housing units can be equipped with any of our linear ball bearings.


Accessory:

End seals 21560.

Precision guide shafts 21595.

Fastening screws 07160 or 07161.

Drawings



Overview of items

Order No.	A	D	D1	D2	D3	E1	E2	H	H1	H2	H3	H4	L	M
21530-081002	35	8	16	3,3	6	20	25	28	13	10	19,5	8	32	M4
21530-121002	43	12	22	4,2	8	23	32	35	18	13	25	10	39	M5
21530-161002	53	16	26	5,2	10	26	40	42	22	13	30	12	43	M6
21530-201002	60	20	32	6,8	11	32	45	50	25	18	34	13	54	M8
21530-251002	78	25	40	8,6	15	40	60	60	30	22	40	15	67	M10
21530-301002	87	30	47	8,6	15	45	68	70	35	22	48	16	79	M10
21530-401002	108	40	62	10,3	18	58	86	90	45	26	60	20	91	M12
21530-501002	132	50	75	14,25	20	50	108	105	50	34	49	20	113	M16