

Item description/product images



Description

Material:

Tool steel or 1.4305 stainless steel.

Version:

Steel hardened and ground.


Stainless steel ground and kolsterised.

Note:


Ball end locating pins are specially designed to ease the locating process. The tendency to jam, caused by the locating hole not being at right angles to the pin or by the pushing force not being parallel to the pin axis, is minimized by the ball-end form (see illustration 1)

Drawing reference:

- 1) Internal thread one side in blind hole
- 2) Internal thread both sides in blind holes
- 3) Internal thread both sides in through hole



Drawings



Overview of items

Order No.	Material	Size	A	B	C	D	E	F	G	H	J	Threaded core hole
03107-05	tool steel	1	5	5	5	6	5	2	M2,5	4,5	R 1	Blind hole
03107-06	tool steel	1	6	6	6	8	6	2	M3	5	R 1	Blind hole
03107-08	tool steel	1	8	8	8	10	8	2	M3	6	R 2	Blind hole
03107-10	tool steel	1	10	10	10	13	10	2,5	M3	6	R 2,5	Blind hole
03107-12	tool steel	1	12	12	12	15	12	3	M4	8	R 3	Blind hole
03107-14	tool steel	1	14	14	14	17	14	3,5	M4	8	R 3,5	Blind hole
03107-16	tool steel	1	16	16	16	20	16	4	M5	10	R 4	Blind hole
03107-20	tool steel	1	20	20	20	25	20	5	M5	10	R 5	Blind hole
03107-25	tool steel	1	25	25	25	25	25	6	M5	10	R 6	Blind hole
03107-30	tool steel	1	30	30	30	30	30	8	M6	12	R 8	Blind hole
03107-40	tool steel	1	40	40	40	40	40	10	M6	12	R 10	Blind hole
03107-50	tool steel	1	50	50	50	50	50	12	M6	12	R 12	Blind hole
03107-505	stainless steel	1	5	5	5	6	5	2	M2,5	4,5	R 1	Blind hole
03107-506	stainless steel	1	6	6	6	8	6	2	M3	5	R 1	Blind hole
03107-508	stainless steel	1	8	8	8	10	8	2	M3	6	R 2	Blind hole
03107-510	stainless steel	1	10	10	10	13	10	2,5	M3	6	R 2,5	Blind hole
03107-512	stainless steel	1	12	12	12	15	12	3	M4	8	R 3	Blind hole

Overview of items

Order No.	Material	Size	A	B	C	D	E	F	G	H	J	Threaded core hole
03107-514	stainless steel	1	14	14	14	17	14	3,5	M4	8	R 3,5	Blind hole
03107-516	stainless steel	1	16	16	16	20	16	4	M5	10	R 4	Blind hole
03107-520	stainless steel	1	20	20	20	25	20	5	M5	10	R 5	Blind hole
03107-1002	tool steel	2	10	10	10	13	10	2,5	M3	6	R 2,5	Blind hole
03107-1202	tool steel	2	12	12	12	15	12	3	M4	8	R 3	Blind hole
03107-1402	tool steel	2	14	14	14	17	14	3,5	M4	8	R 3,5	Blind hole
03107-1602	tool steel	2	16	16	16	20	16	4	M5	10	R 4	Blind hole
03107-2002	tool steel	2	20	20	20	25	20	5	M5	10	R 5	Blind hole
03107-2502	tool steel	2	25	25	25	25	25	6	M5	10	R 6	Blind hole
03107-3002	tool steel	2	30	30	30	30	30	8	M6	12	R 8	Blind hole
03107-4002	tool steel	2	40	40	40	40	40	10	M6	12	R 10	Blind hole
03107-5002	tool steel	2	50	50	50	50	50	12	M6	12	R 12	Blind hole
03107-51002	stainless steel	2	10	10	10	13	10	2,5	M3	6	R 2,5	Blind hole
03107-51202	stainless steel	2	12	12	12	15	12	3	M4	8	R 3	Blind hole
03107-51402	stainless steel	2	14	14	14	17	14	3,5	M4	8	R 3,5	Blind hole
03107-51602	stainless steel	2	16	16	16	20	16	4	M5	10	R 4	Blind hole
03107-52002	stainless steel	2	20	20	20	25	20	5	M5	10	R 5	Blind hole
03107-0502	tool steel	3	5	5	5	6	5	2	M2,5	4,5	R 1	Through hole
03107-0602	tool steel	3	6	6	6	8	6	2	M3	5	R 1	Through hole
03107-0802	tool steel	3	8	8	8	10	8	2	M3	6	R 2	Through hole
03107-50502	stainless steel	3	5	5	5	6	5	2	M2,5	4,5	R 1	Through hole
03107-50602	stainless steel	3	6	6	6	8	6	2	M3	5	R 1	Through hole
03107-50802	stainless steel	3	8	8	8	10	8	2	M3	6	R 2	Through hole