


Item description/product images



Description

Material:

Housing aluminium

Version:

Housing bright.

Note:

Ready to install linear housing units consisting of an extruded aluminium housing with two self-aligning linear ball bearings 21510 and seals both sides. The bearings are secured in the housing with DIN 472 circlips.

Recommended shaft tolerance: h6.

Load ratings according to the linear ball bearing specifications (x2).

On request:

Linear housing units can be equipped with any of our linear ball bearings.


Accessory:

End seals 21560.

Precision guide shafts 21595.

Fastening screws 07160 or 07161.

Drawings



Overview of items

Order No.	A	D	D1	D2	D3	E1	E2	H	H1	H2	H3	H4	L	M
21540-081002	35	8	16	4,2	8	35	25	28	13	13	19,5	8	62	M5
21540-121002	43	12	22	5,2	10	40	30	35	18	13	25	10	76	M6
21540-161002	53	16	26	5,2	10	45	36	42	22	13	30	12	84	M6
21540-201002	60	20	32	6,8	11	55	45	50	25	18	34	13	104	M8
21540-251002	78	25	40	8,6	15	70	54	60	30	22	40	15	130	M10
21540-301002	87	30	47	10,3	18	85	62	70	35	26	48	16	152	M12
21540-401002	108	40	62	14,25	20	100	80	90	45	34	60	20	176	M16
21540-501002	132	50	75	14,25	20	125	100	105	50	34	49	20	224	M16