

Item description/product images

**Description****Material:**

Steel or stainless steel 1.4301.

Version:

Steel trivalent blue passivated.

Stainless steel bright.

Note:

Adjustable latches are secure locking systems for industrial applications. By exceeding the dead centre they resist vibration.

After the hook is engaged with the catch plate, the parts to be locked can be drawn together by up to 5 mm by pushing the lever down.

To compensate for tolerances or to create enough tension, the hook length can be adjusted using the M5 threaded spindle.

The latches can be screwed down or riveted.

Any catch plate can be combined with any latch.

Order required catch plate version separately.

The retaining force F1 applies to the latch, not the catch plate.

Accessory:

Catch plate 05540.

Drawing reference:


Form A standard

Form B with safety catch

Form C with padlock bracket

1) Hole arrangements for assembly with catch plate

Drawings



Overview of items

Order No.	Main material	Form	Product type	Retaining force F1 N
05535-1541091	steel	A	standard	2000
05535-1541092	stainless steel	A	standard	2000
05535-2641351	steel	B	standard	3000
05535-2641352	stainless steel	B	standard	3000
05540-3420721	steel	C	with padlock hole	1000
05540-3420722	stainless steel	C	with padlock hole	1000