

Item description/product images



Description


Material:

Wheel body welded steel construction.
Tread Extrathane®.

Note:

Extrathane treads are elastic, resist abrasion, gentle to floors, low-noise and have particularly high elastic restoration after long standing.
Application temperature from -40 °C to +80 °C.
Suitable as replacement rollers for the castors 95030 and 95032.

Drawings



Overview of items

Order No.	Wheel bearing	D	D1	B	B1	Permissible load kg
95060-12550	Ball bearing	125	20	50	60	500
95060-16050	Ball bearing	160	20	50	60	700
95060-20050	Ball bearing	200	20	50	60	1000
95060-25060	Ball bearing	250	25	60	70	1350

Overview of items
