

## Item description/product images



### Description

**Material:**

Housing steel plate.  
Wheel treads solid rubber.  
Wheel rims polyamide.


**Version:**

Housing press formed.  
Double ball bearing in the castor head.  
Plain bearing in wheels.

**Note:**

Wheel axle bolted.  
Solid rubber tyres are shock and impact proof and non-corroding.

## Drawings



## Overview of items

| Order No.    | Item          | Version 1              | Wheel bearing | A  | B  | D   | H   | R  | Permissible load kg |
|--------------|---------------|------------------------|---------------|----|----|-----|-----|----|---------------------|
| 95012-080251 | Fixed castor  | without locking system | plain bearing | -  | 25 | 80  | 111 | -  | 60                  |
| 95012-100321 | Fixed castor  | without locking system | plain bearing | -  | 32 | 100 | 136 | -  | 90                  |
| 95012-125251 | Fixed castor  | without locking system | plain bearing | -  | 25 | 125 | 161 | -  | 80                  |
| 95012-125321 | Fixed castor  | without locking system | plain bearing | -  | 32 | 125 | 161 | -  | 100                 |
| 95012-08025  | Swivel castor | without locking system | plain bearing | 40 | 25 | 80  | 111 | 80 | 60                  |

## Overview of items

| Order No.    | Item          | Version 1                    | Wheel bearing | A  | B  | D   | H   | R     | Permissible load kg |
|--------------|---------------|------------------------------|---------------|----|----|-----|-----|-------|---------------------|
| 95012-10032  | Swivel castor | without locking system       | plain bearing | 40 | 32 | 100 | 136 | 90    | 90                  |
| 95012-12525  | Swivel castor | without locking system       | plain bearing | 40 | 25 | 125 | 161 | 102,5 | 80                  |
| 95012-12532  | Swivel castor | without locking system       | plain bearing | 40 | 32 | 125 | 161 | 102,5 | 100                 |
| 95012-080252 | Swivel castor | with stop-fix locking system | plain bearing | 40 | 25 | 80  | 111 | 80    | 60                  |
| 95012-100322 | Swivel castor | with stop-fix locking system | plain bearing | 40 | 32 | 100 | 136 | 90    | 90                  |
| 95012-125252 | Swivel castor | with stop-fix locking system | plain bearing | 40 | 25 | 125 | 161 | 102,5 | 80                  |
| 95012-125322 | Swivel castor | with stop-fix locking system | plain bearing | 40 | 32 | 125 | 161 | 102,5 | 100                 |