

Item description/product images

**Description****Material:**

Steel.

Version:


Hardened and ground (HRC 60 ±2).

Note:

The locating pins are designed to make the joining process easier. Used in combination with hardened locating bushes 02026, they enable exact, low-wear, and fast changes of the workpiece.

Versions D1 = 5 and D1 = 6 do not have an internal thread.

Drawings



Overview of items

Order No.	Form	Version 1	D1	D2	H	H1	H2	G	R	T
02025-205	B	short	5	3	8	3	5	-	1,50	-
02025-206	B	short	6	4	10	4	6	-	1,80	-
02025-208	B	short	8	6	11,4	6	7,4	M2,5	2,5	5
02025-210	B	short	10	7	13,7	7	9,7	M2,5	3	5
02025-212	B	short	12	8	16	8	12	M3	3,5	6
02025-216	B	short	16	12	20	12	15	M4	5	8
02025-220	B	short	20	14	25,5	14	19,5	M5	6	10
02025-305	B	long	5	3	10	3	5	-	1,50	-
02025-306	B	long	6	4	12	4	6	-	1,80	-
02025-308	B	long	8	6	17,4	6	7,4	M2,5	2,5	5
02025-310	B	long	10	7	21,7	7	9,7	M2,5	3	5
02025-312	B	long	12	8	24	8	12	M3	3,5	6
02025-316	B	long	16	12	29	12	15	M4	5	8
02025-320	B	long	20	14	35,5	14	19,5	M5	6	10

