

Item description/product images



Description

Material:

Housing steel plate.

Wheel body PA 6 with vulcanised elastic solid rubber tyre.

Version:

Housing press formed.

Double ball bearing with ball shield in castor head.


Roller bearings in the wheels.

Note:

Wheel axle bolted.

Wheels are shock and impact proof.

Drawings



Overview of items

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	R	Permissible load kg
95018-100371	Fixed castor	without locking system	roller bearing	-	32	-	60	85	100	9	125	100	80	-	170
95018-125371	Fixed castor	without locking system	roller bearing	-	37	-	60	85	125	9	150	100	80	-	200
95018-160501	Fixed castor	without locking system	roller bearing	-	50	75	80	110	160	11	195	140	105	-	350
95018-200501	Fixed castor	without locking system	roller bearing	-	50	75	80	110	200	11	235	140	105	-	400
95018-10037	Swivel castor	without locking system	roller bearing	36	32	-	60	85	100	9	125	100	80	86	170
95018-12537	Swivel castor	without locking system	roller bearing	40	37	-	60	85	125	9	150	100	80	102,5	200
95018-16050	Swivel castor	without locking system	roller bearing	60	50	75	80	110	160	11	195	140	105	140	350

Overview of items

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	R	Permissible load kg
95018-20050	Swivel castor	without locking system	roller bearing	65	50	75	80	110	200	11	235	140	105	165	400
95018-100372	Swivel castor	with stop-fix locking system	roller bearing	36	32	-	60	85	100	9	125	100	80	86	170
95018-125372	Swivel castor	with stop-fix locking system	roller bearing	40	37	-	60	85	125	9	150	100	80	102,5	200
95018-160502	Swivel castor	with stop-fix locking system	roller bearing	60	50	75	80	110	160	11	195	140	105	140	350
95018-200502	Swivel castor	with stop-fix locking system	roller bearing	65	50	75	80	110	200	11	235	140	105	165	400