

## Item description/product images



## Description

**Material:**

Housing thick steel plate.  
Wheels high-quality PA 6.


**Version:**

Housing press formed.  
Swivel castor housing with strong fork and base plate, very robust centre pin bolted and secured. The swivel head is additionally reinforced with specially formed and hardened bearing shells.

**Note:**

The hardened bearing shells make these castors particularly shock and impact proof. The wheels have high abrasion resistance. Wheel axle bolted.

## Drawings



## Overview of items

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	R	Permissible load kg
95040-07532	Swivel castor	without locking system	plain bearing	45	32	60	-	85	75	9	118	100	80	82,5	300
95040-075323	Swivel castor	without locking system	ball bearing	45	32	60	-	85	75	9	118	100	80	82,5	300
95040-10037	Swivel castor	without locking system	plain bearing	45	37	60	-	85	100	9	140	100	80	95	500
95040-100373	Swivel castor	without locking system	ball bearing	45	37	60	-	85	100	9	140	100	80	95	500
95040-12540	Swivel castor	without locking system	plain bearing	45	40	60	-	85	125	9	165	100	80	107,5	700
95040-125403	Swivel castor	without locking system	ball bearing	45	40	60	-	85	125	9	165	100	80	107,5	700
95040-15050	Swivel castor	without locking system	plain bearing	65	50	80	75	110	150	11	197	140	105	140	800
95040-150503	Swivel castor	without locking system	ball bearing	65	50	80	75	110	150	11	197	140	105	140	800