

Item description/product images



Description

Material:

Housing and wheel rim steel plate.

Tyres solid rubber.

Wheel hub steel tube.

Version:

Housing and rim press formed.

Double ball bearing with ball shield in castor head.


Roller bearings in the wheels.

Note:


Wheel axle bolted.

Drawings

swivel castor



Drawings



Overview of items

Order No.	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	L	L1	H	R	Permissible load kg
95016-08025	without locking system	roller bearing	38	25	-	60	85	80	9	100	80	102	78	50
95016-10030	without locking system	roller bearing	36	30	-	60	85	100	9	100	80	125	86	70
95016-12538	without locking system	roller bearing	40	37,5	-	60	85	125	9	100	80	150	102,5	100
95016-16040	without locking system	roller bearing	60	40	75	80	110	160	11	140	105	195	140	135
95016-20050	without locking system	roller bearing	65	50	75	80	110	200	11	140	105	235	165	205