


Item description/product images



Elastic bonding and sealing

Description

Note:

* Skin formation time.

Note:

Safety data sheets (see downloads) can be found officially and in various languages on the internet under the search term: 'Henkel Documents'.

General:

For permanently elastic adhesive joints and a simultaneous sealant effect against water and dust, etc.

LOCTITE permanently elastic adhesive and sealant, 97990-5366310

Clear paste. Is used as an adhesive to optimally seal, glue and protect. Typical applications are the sealing of wall panels on trains, sealing heat sources (ovens, heat exchangers, steam pipes, hot water boilers), protection and insulation of switchboxes and gluing HCR silicon. Also used in the maintenance sector.

Temperature resistant from -50 °C to +200 °C.

LOCTITE permanently elastic black adhesive and sealant, 97990-5368310

Black paste. Used mainly to seal. Is also suitable for gluing and high temperature applications. Used in many industrial sectors, such as electrical household equipment and the automobile and aerospace industries.

Temperature resistant from -50 °C to +200 °C.

Overview of items

Order No.	Container	Intern. Ident. No.	Hardening system	Handling strength in min.	Tensile strength N/mm ²	Elongation %	Shore grade
97990-5366310	310 ml cartridge	5366	air humidity	5*	2	530	25A
97990-5368310	310 ml cartridge	5368	air humidity	5*	2	435	26A