

## Item description/product images



### Description

#### Material:

Metal parts steel grade 5.6 or stainless steel.  
Elastomer natural rubber, medium hardness, Shore 55A.

#### Version:

Steel electro zinc-plated.  
Stainless steel bright.

#### Note:

Rubber buffers are used, among other things for mounting aggregates and as elastic buffers to limit the travel of moving masses.

Due to the material composition, rubber buffers are contact-colouring, which can lead to abrasion marks and discolouration on e.g. floors or contact surfaces.

Rubber buffers made of light grey EPDM that are not contact-colouring are available on request.


#### Temperature range:

-30 °C to +80 °C

#### On request:

Other Shore grades.

## Drawings



## Overview of items

Order No.	Main material	D	H	G	L	Spring stiffness N/mm	Load N
26106-00800855	steel	8	8	M3	6	40	40
26106-01001055	steel	10	10	M4	10	35	35
26106-01001555	steel	10	15	M4	10	26	40
26106-01500655	steel	15	6	M4	10	175	88
26106-01500855	steel	15	8	M4	10	187	187
26106-01501055	steel	15	10	M4	10	100	100
26106-01501555	steel	15	15	M4	10	50	100
26106-02000555	steel	20	5	M6	18	135	95
26106-02000855	steel	20	8	M6	18	250	250
26106-02001055	steel	20	10	M6	18	240	240
26106-02001555	steel	20	15	M6	18	110	220
26106-02002055	steel	20	20	M6	18	75	225
26106-02002555	steel	20	25	M6	18	65	227,5
26106-02500855	steel	25	8	M6	18	850	850
26106-02501055	steel	25	10	M6	18	400	400
26106-02501555	steel	25	15	M6	18	210	420
26106-02502055	steel	25	20	M6	18	140	420

## Overview of items

Order No.	Main material	D	H	G	L	Spring stiffness N/mm	Load N
26106-02502555	steel	25	25	M6	18	100	350
26106-02503055	steel	25	30	M6	18	79	316
26106-03001555	steel	30	15	M8	23	270	540
26106-03002055	steel	30	20	M8	23	238	714
26106-03002555	steel	30	25	M8	23	153	535,5
26106-03003055	steel	30	30	M8	23	127	508
26106-03004055	steel	30	40	M8	23	88	528
26106-04001555	steel	40	15	M8	23	710	1420
26106-04002055	steel	40	20	M8	23	365	1095
26106-04003055	steel	40	30	M8	23	205	820
26106-04004055	steel	40	40	M8	23	143	858
26106-05002055	steel	50	20	M10	28	646	1938
26106-05003055	steel	50	30	M10	28	354	1416
26106-05004055	steel	50	40	M10	28	230	1380
26106-05005055	steel	50	50	M10	28	160	1280
26106-06004055	steel	60	40	M10	28	317	1902
26106-07002555	steel	70	25	M10	28	980	3430
26106-07004555	steel	70	45	M10	28	438	3066
26106-07502555	steel	75	25	M12	37	1318	4613
26106-07504055	steel	75	40	M12	37	643	3858
26106-07505055	steel	75	50	M12	37	472	3776
26106-07505555	steel	75	55	M12	37	310	3100
26106-008008551	stainless steel	8	8	M3	8	40	40
26106-010010551	stainless steel	10	10	M4	10	35	35
26106-015015551	stainless steel	15	15	M4	10	50	100
26106-020015551	stainless steel	20	15	M6	18	110	220
26106-025020551	stainless steel	25	20	M6	18	140	420
26106-030030551	stainless steel	30	30	M8	23	127	508
26106-040030551	stainless steel	40	30	M8	23	205	820