

Item description/product images



colour codes:



Description

Product description:

The newly designed Bighand tubular handle with its ergonomic oval shape and selected tube size provides a secure and comfortable grip. Its timeless elegant design makes it attractive and the variable colour scheme means it can be optimally adapted to its surroundings.

Material:

Oval tube aluminium.
End piece thermoplastic polyamide.
End cap thermoplastic polyamide.
Adapter bush stainless steel.

Version:

Oval tube black grey powder-coated (glossy), black anodised (matt) or natural tone anodised (matt).
End piece black grey RAL 7021.
End cap black grey RAL7021, pure orange RAL 2004, rape yellow RAL 1021, traffic red RAL 3020, signal green RAL 6032 or traffic blue RAL 5017.

Note for ordering:

Δ Enter the required colour code here.

Note:

Fastening materials are not supplied.
Cap screws with thread lock are recommended for a secure and permanent hold.

Temperature range:

Permanent temperature max. 100 °C.
Short time use up to 180 °C.

Assembly:

The end pieces are designed so that the tubular handle can be fastened either from the front or rear. DIN M8 cap screws or hex head screws are provided for this purpose. After mounting, the end caps can be pressed in by hand. Slots are provided on both sides of the end caps so that they can be removed with a screwdriver without damaging them.

On request:

Special lengths "A".


Accessory:

07160 Socket head screws DIN 912 / DIN EN ISO 4762 with thread lock
07160 Socket head screws DIN 912 / DIN EN ISO 4762
07171 Hex head screws DIN 933 / DIN-EN-ISO 4017
07210 Hex nuts DIN 934 / DIN EN ISO 4032 / DIN EN 24032
07300 Washers DIN 125 / DIN EN ISO 7089 Form A

Item description/product images



Drawings



Overview of items

Order No.	Colour Oval grip	Surface finish body	Colour Cover	A	B	D	H	L	Load capacity N
06948-01-1801	black grey	powder-coated	black grey RAL 7021	180	39,2	8	75,5	213,4	1000
06948-01-2001	black grey	powder-coated	black grey RAL 7021	200	39,2	8	75,5	233,4	1000
06948-01-2501	black grey	powder-coated	black grey RAL 7021	250	39,2	8	75,5	283,4	1000
06948-01-3001	black grey	powder-coated	black grey RAL 7021	300	39,2	8	75,5	333,4	1000

Overview of items

Order No.	Colour Oval grip	Surface finish body	Colour Cover	A	B	D	H	L	Load capacity N
06948-01-3501	black grey	powder-coated	black grey RAL 7021	350	39,2	8	75,5	383,4	1000
06948-01-4001	black grey	powder-coated	black grey RAL 7021	400	39,2	8	75,5	433,4	1000
06948-01-5001	black grey	powder-coated	black grey RAL 7021	500	39,2	8	75,5	533,4	1000
06948-01-6001	black grey	powder-coated	black grey RAL 7021	600	39,2	8	75,5	633,4	1000
06948-01-1802	black grey	powder-coated	orange RAL 2004	180	39,2	8	75,5	213,4	1000
06948-01-2002	black grey	powder-coated	orange RAL 2004	200	39,2	8	75,5	233,4	1000
06948-01-2502	black grey	powder-coated	orange RAL 2004	250	39,2	8	75,5	283,4	1000
06948-01-3002	black grey	powder-coated	orange RAL 2004	300	39,2	8	75,5	333,4	1000
06948-01-3502	black grey	powder-coated	orange RAL 2004	350	39,2	8	75,5	383,4	1000
06948-01-4002	black grey	powder-coated	orange RAL 2004	400	39,2	8	75,5	433,4	1000
06948-01-5002	black grey	powder-coated	orange RAL 2004	500	39,2	8	75,5	533,4	1000
06948-01-6002	black grey	powder-coated	orange RAL 2004	600	39,2	8	75,5	633,4	1000
06948-01-18016	black grey	powder-coated	colza yellow RAL 1021	180	39,2	8	75,5	213,4	1000
06948-01-20016	black grey	powder-coated	colza yellow RAL 1021	200	39,2	8	75,5	233,4	1000
06948-01-25016	black grey	powder-coated	colza yellow RAL 1021	250	39,2	8	75,5	283,4	1000
06948-01-30016	black grey	powder-coated	colza yellow RAL 1021	300	39,2	8	75,5	333,4	1000
06948-01-35016	black grey	powder-coated	colza yellow RAL 1021	350	39,2	8	75,5	383,4	1000
06948-01-40016	black grey	powder-coated	colza yellow RAL 1021	400	39,2	8	75,5	433,4	1000
06948-01-50016	black grey	powder-coated	colza yellow RAL 1021	500	39,2	8	75,5	533,4	1000
06948-01-60016	black grey	powder-coated	colza yellow RAL 1021	600	39,2	8	75,5	633,4	1000
06948-01-18084	black grey	powder-coated	traffic red RAL 3020	180	39,2	8	75,5	213,4	1000
06948-01-20084	black grey	powder-coated	traffic red RAL 3020	200	39,2	8	75,5	233,4	1000
06948-01-25084	black grey	powder-coated	traffic red RAL 3020	250	39,2	8	75,5	283,4	1000
06948-01-30084	black grey	powder-coated	traffic red RAL 3020	300	39,2	8	75,5	333,4	1000
06948-01-35084	black grey	powder-coated	traffic red RAL 3020	350	39,2	8	75,5	383,4	1000
06948-01-40084	black grey	powder-coated	traffic red RAL 3020	400	39,2	8	75,5	433,4	1000
06948-01-50084	black grey	powder-coated	traffic red RAL 3020	500	39,2	8	75,5	533,4	1000
06948-01-60084	black grey	powder-coated	traffic red RAL 3020	600	39,2	8	75,5	633,4	1000
06948-01-18086	black grey	powder-coated	signal green RAL6032	180	39,2	8	75,5	213,4	1000
06948-01-20086	black grey	powder-coated	signal green RAL6032	200	39,2	8	75,5	233,4	1000
06948-01-25086	black grey	powder-coated	signal green RAL6032	250	39,2	8	75,5	283,4	1000
06948-01-30086	black grey	powder-coated	signal green RAL6032	300	39,2	8	75,5	333,4	1000
06948-01-35086	black grey	powder-coated	signal green RAL6032	350	39,2	8	75,5	383,4	1000
06948-01-40086	black grey	powder-coated	signal green RAL6032	400	39,2	8	75,5	433,4	1000
06948-01-50086	black grey	powder-coated	signal green RAL6032	500	39,2	8	75,5	533,4	1000
06948-01-60086	black grey	powder-coated	signal green RAL6032	600	39,2	8	75,5	633,4	1000
06948-01-18087	black grey	powder-coated	blue RAL5017	180	39,2	8	75,5	213,4	1000
06948-01-20087	black grey	powder-coated	blue RAL5017	200	39,2	8	75,5	233,4	1000
06948-01-25087	black grey	powder-coated	blue RAL5017	250	39,2	8	75,5	283,4	1000
06948-01-30087	black grey	powder-coated	blue RAL5017	300	39,2	8	75,5	333,4	1000
06948-01-35087	black grey	powder-coated	blue RAL5017	350	39,2	8	75,5	383,4	1000
06948-01-40087	black grey	powder-coated	blue RAL5017	400	39,2	8	75,5	433,4	1000
06948-01-50087	black grey	powder-coated	blue RAL5017	500	39,2	8	75,5	533,4	1000
06948-01-60087	black grey	powder-coated	blue RAL5017	600	39,2	8	75,5	633,4	1000
06948-01-180011	black	anodised	black grey RAL 7021	180	39,2	8	75,5	213,4	1000
06948-01-200011	black	anodised	black grey RAL 7021	200	39,2	8	75,5	233,4	1000
06948-01-250011	black	anodised	black grey RAL 7021	250	39,2	8	75,5	283,4	1000
06948-01-300011	black	anodised	black grey RAL 7021	300	39,2	8	75,5	333,4	1000
06948-01-350011	black	anodised	black grey RAL 7021	350	39,2	8	75,5	383,4	1000
06948-01-400011	black	anodised	black grey RAL 7021	400	39,2	8	75,5	433,4	1000
06948-01-500011	black	anodised	black grey RAL 7021	500	39,2	8	75,5	533,4	1000
06948-01-600011	black	anodised	black grey RAL 7021	600	39,2	8	75,5	633,4	1000
06948-01-180012	black	anodised	orange RAL 2004	180	39,2	8	75,5	213,4	1000
06948-01-200012	black	anodised	orange RAL 2004	200	39,2	8	75,5	233,4	1000
06948-01-250012	black	anodised	orange RAL 2004	250	39,2	8	75,5	283,4	1000
06948-01-300012	black	anodised	orange RAL 2004	300	39,2	8	75,5	333,4	1000
06948-01-350012	black	anodised	orange RAL 2004	350	39,2	8	75,5	383,4	1000
06948-01-400012	black	anodised	orange RAL 2004	400	39,2	8	75,5	433,4	1000
06948-01-500012	black	anodised	orange RAL 2004	500	39,2	8	75,5	533,4	1000
06948-01-600012	black	anodised	orange RAL 2004	600	39,2	8	75,5	633,4	1000
06948-01-1800116	black	anodised	colza yellow RAL 1021	180	39,2	8	75,5	213,4	1000
06948-01-2000116	black	anodised	colza yellow RAL 1021	200	39,2	8	75,5	233,4	1000
06948-01-2500116	black	anodised	colza yellow RAL 1021	250	39,2	8	75,5	283,4	1000
06948-01-3000116	black	anodised	colza yellow RAL 1021	300	39,2	8	75,5	333,4	1000

Overview of items

Order No.	Colour Oval grip	Surface finish body	Colour Cover	A	B	D	H	L	Load capacity N
06948-01-3500116	black	anodised	colza yellow RAL 1021	350	39,2	8	75,5	383,4	1000
06948-01-4000116	black	anodised	colza yellow RAL 1021	400	39,2	8	75,5	433,4	1000
06948-01-5000116	black	anodised	colza yellow RAL 1021	500	39,2	8	75,5	533,4	1000
06948-01-6000116	black	anodised	colza yellow RAL 1021	600	39,2	8	75,5	633,4	1000
06948-01-1800184	black	anodised	traffic red RAL 3020	180	39,2	8	75,5	213,4	1000
06948-01-2000184	black	anodised	traffic red RAL 3020	200	39,2	8	75,5	233,4	1000
06948-01-2500184	black	anodised	traffic red RAL 3020	250	39,2	8	75,5	283,4	1000
06948-01-3000184	black	anodised	traffic red RAL 3020	300	39,2	8	75,5	333,4	1000
06948-01-3500184	black	anodised	traffic red RAL 3020	350	39,2	8	75,5	383,4	1000
06948-01-4000184	black	anodised	traffic red RAL 3020	400	39,2	8	75,5	433,4	1000
06948-01-5000184	black	anodised	traffic red RAL 3020	500	39,2	8	75,5	533,4	1000
06948-01-6000184	black	anodised	traffic red RAL 3020	600	39,2	8	75,5	633,4	1000
06948-01-1800186	black	anodised	signal green RAL6032	180	39,2	8	75,5	213,4	1000
06948-01-2000186	black	anodised	signal green RAL6032	200	39,2	8	75,5	233,4	1000
06948-01-2500186	black	anodised	signal green RAL6032	250	39,2	8	75,5	283,4	1000
06948-01-3000186	black	anodised	signal green RAL6032	300	39,2	8	75,5	333,4	1000
06948-01-3500186	black	anodised	signal green RAL6032	350	39,2	8	75,5	383,4	1000
06948-01-4000186	black	anodised	signal green RAL6032	400	39,2	8	75,5	433,4	1000
06948-01-5000186	black	anodised	signal green RAL6032	500	39,2	8	75,5	533,4	1000
06948-01-6000186	black	anodised	signal green RAL6032	600	39,2	8	75,5	633,4	1000
06948-01-1800187	black	anodised	blue RAL5017	180	39,2	8	75,5	213,4	1000
06948-01-2000187	black	anodised	blue RAL5017	200	39,2	8	75,5	233,4	1000
06948-01-2500187	black	anodised	blue RAL5017	250	39,2	8	75,5	283,4	1000
06948-01-3000187	black	anodised	blue RAL5017	300	39,2	8	75,5	333,4	1000
06948-01-3500187	black	anodised	blue RAL5017	350	39,2	8	75,5	383,4	1000
06948-01-4000187	black	anodised	blue RAL5017	400	39,2	8	75,5	433,4	1000
06948-01-5000187	black	anodised	blue RAL5017	500	39,2	8	75,5	533,4	1000
06948-01-6000187	black	anodised	blue RAL5017	600	39,2	8	75,5	633,4	1000
06948-01-180031	natural	anodised	black grey RAL 7021	180	39,2	8	75,5	213,4	1000
06948-01-200031	natural	anodised	black grey RAL 7021	200	39,2	8	75,5	233,4	1000
06948-01-250031	natural	anodised	black grey RAL 7021	250	39,2	8	75,5	283,4	1000
06948-01-300031	natural	anodised	black grey RAL 7021	300	39,2	8	75,5	333,4	1000
06948-01-350031	natural	anodised	black grey RAL 7021	350	39,2	8	75,5	383,4	1000
06948-01-400031	natural	anodised	black grey RAL 7021	400	39,2	8	75,5	433,4	1000
06948-01-500031	natural	anodised	black grey RAL 7021	500	39,2	8	75,5	533,4	1000
06948-01-600031	natural	anodised	black grey RAL 7021	600	39,2	8	75,5	633,4	1000
06948-01-180032	natural	anodised	orange RAL 2004	180	39,2	8	75,5	213,4	1000
06948-01-200032	natural	anodised	orange RAL 2004	200	39,2	8	75,5	233,4	1000
06948-01-250032	natural	anodised	orange RAL 2004	250	39,2	8	75,5	283,4	1000
06948-01-300032	natural	anodised	orange RAL 2004	300	39,2	8	75,5	333,4	1000
06948-01-350032	natural	anodised	orange RAL 2004	350	39,2	8	75,5	383,4	1000
06948-01-400032	natural	anodised	orange RAL 2004	400	39,2	8	75,5	433,4	1000
06948-01-500032	natural	anodised	orange RAL 2004	500	39,2	8	75,5	533,4	1000
06948-01-600032	natural	anodised	orange RAL 2004	600	39,2	8	75,5	633,4	1000
06948-01-1800316	natural	anodised	colza yellow RAL 1021	180	39,2	8	75,5	213,4	1000
06948-01-2000316	natural	anodised	colza yellow RAL 1021	200	39,2	8	75,5	233,4	1000
06948-01-2500316	natural	anodised	colza yellow RAL 1021	250	39,2	8	75,5	283,4	1000
06948-01-3000316	natural	anodised	colza yellow RAL 1021	300	39,2	8	75,5	333,4	1000
06948-01-3500316	natural	anodised	colza yellow RAL 1021	350	39,2	8	75,5	383,4	1000
06948-01-4000316	natural	anodised	colza yellow RAL 1021	400	39,2	8	75,5	433,4	1000
06948-01-5000316	natural	anodised	colza yellow RAL 1021	500	39,2	8	75,5	533,4	1000
06948-01-6000316	natural	anodised	colza yellow RAL 1021	600	39,2	8	75,5	633,4	1000
06948-01-1800384	natural	anodised	traffic red RAL 3020	180	39,2	8	75,5	213,4	1000
06948-01-2000384	natural	anodised	traffic red RAL 3020	200	39,2	8	75,5	233,4	1000
06948-01-2500384	natural	anodised	traffic red RAL 3020	250	39,2	8	75,5	283,4	1000
06948-01-3000384	natural	anodised	traffic red RAL 3020	300	39,2	8	75,5	333,4	1000
06948-01-3500384	natural	anodised	traffic red RAL 3020	350	39,2	8	75,5	383,4	1000
06948-01-4000384	natural	anodised	traffic red RAL 3020	400	39,2	8	75,5	433,4	1000
06948-01-5000384	natural	anodised	traffic red RAL 3020	500	39,2	8	75,5	533,4	1000
06948-01-6000384	natural	anodised	traffic red RAL 3020	600	39,2	8	75,5	633,4	1000
06948-01-1800386	natural	anodised	signal green RAL6032	180	39,2	8	75,5	213,4	1000
06948-01-2000386	natural	anodised	signal green RAL6032	200	39,2	8	75,5	233,4	1000
06948-01-2500386	natural	anodised	signal green RAL6032	250	39,2	8	75,5	283,4	1000
06948-01-3000386	natural	anodised	signal green RAL6032	300	39,2	8	75,5	333,4	1000

Overview of items

Order No.	Colour Oval grip	Surface finish body	Colour Cover	A	B	D	H	L	Load capacity N
06948-01-3500386	natural	anodised	signal green RAL6032	350	39,2	8	75,5	383,4	1000
06948-01-4000386	natural	anodised	signal green RAL6032	400	39,2	8	75,5	433,4	1000
06948-01-5000386	natural	anodised	signal green RAL6032	500	39,2	8	75,5	533,4	1000
06948-01-6000386	natural	anodised	signal green RAL6032	600	39,2	8	75,5	633,4	1000
06948-01-1800387	natural	anodised	blue RAL5017	180	39,2	8	75,5	213,4	1000
06948-01-2000387	natural	anodised	blue RAL5017	200	39,2	8	75,5	233,4	1000
06948-01-2500387	natural	anodised	blue RAL5017	250	39,2	8	75,5	283,4	1000
06948-01-3000387	natural	anodised	blue RAL5017	300	39,2	8	75,5	333,4	1000
06948-01-3500387	natural	anodised	blue RAL5017	350	39,2	8	75,5	383,4	1000
06948-01-4000387	natural	anodised	blue RAL5017	400	39,2	8	75,5	433,4	1000
06948-01-5000387	natural	anodised	blue RAL5017	500	39,2	8	75,5	533,4	1000
06948-01-6000387	natural	anodised	blue RAL5017	600	39,2	8	75,5	633,4	1000