

Item description/product images



Description

Material:

Sleeve and spring stainless steel.
Pin stainless steel or POM.

Version:


Pins, white POM, temperature-resistant to +50°C.

Note:

Smooth version to press-in.

A ^{H7} tolerance is recommended for the receiving hole with diameter D.

Drawings



Overview of items

Order No.	Component material	D	D1	D2	L	L1	L2	L3	H	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
03077-04	250 mm / M12x1 / M8	4	2,8	4,6	10,7	0,9	1,8	5,6	2,7	3	8,2
03077-05	250 mm / M12x1 / M8	5	3,8	5,6	12	0,9	2,1	6	4	3,3	9
03077-06	250 mm / M12x1 / M8	6	4,8	6,5	15	1	2,3	8,2	5,5	6,1	12
03077-08	250 mm / M12x1 / M8	8	6,2	8,5	18	1,1	2,9	9,5	6,5	10,7	17
03077-10	250 mm / M12x1 / M8	10	8	11	26	1,5	4,2	14,3	8	16,2	29
03077-204	3-axis vice with 50 mm riser plate	4	2,8	4,6	10,7	0,9	1,8	5,6	2,7	3	8,2
03077-205	3-axis vice with 50 mm riser plate	5	3,8	5,6	12	0,9	2,1	6	4	3,3	9
03077-206	3-axis vice with 50 mm riser plate	6	4,8	6,5	15	1	2,3	8,2	5,5	6,1	12
03077-208	3-axis vice with 50 mm riser plate	8	6,2	8,5	18	1,1	2,9	9,5	6,5	10,7	17
03077-210	3-axis vice with 50 mm riser plate	10	8	11	26	1,5	4,2	14,3	8	16,2	29