

Item description/product images



Description

Material:




Special steel

Version:Hardened to 780 ± 40 HV 10 and ground.**Note:**

All bushes have the bore size marked on the upper face.

Form K are quick-change bushes. Dowels or coiled spring pins together with DIN 173-1 flathead screws can be used in place of the stop pin.



The bayonet mount is secured with DIN 173-1 drill bush clamps together with DIN 912 socket head screws.

Quick-change drill bush Form K
with DIN 172 bush with collar
or DIN 179 bushQuick-change drill bush Form K
with DIN 172 bush with collar
or DIN 179 bushExchangeable drill bush Form L
with DIN 172 bush with collar
or DIN 179 bush


E2 = Hole spacing when using dowels or coiled spring pins.

Diameter D1 over 15 mm increase in size by 0.5 mm.

Drawings

Form L
exchangeable bush

dimensions same
as Form K



Overview of items

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-K0240X10	K	2 mm steps	2,4	8	15	4,5	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0240X16	K	normally closed	2,4	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0250X10	K	2 mm steps	2,5	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0250X16	K	normally closed	2,5	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0260X10	K	2 mm steps	2,6	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0260X16	K	normally closed	2,6	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0270X10	K	2 mm steps	2,7	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0270X16	K	normally closed	2,7	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0280X10	K	2 mm steps	2,8	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0280X16	K	normally closed	2,8	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0290X10	K	2 mm steps	2,9	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0290X16	K	normally closed	2,9	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0300X10	K	2 mm steps	3	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0300X16	K	normally closed	3	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0310X10	K	2 mm steps	3,1	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0310X16	K	normally closed	3,1	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0320X10	K	2 mm steps	3,2	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0320X16	K	normally closed	3,2	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0330X10	K	2 mm steps	3,3	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0330X16	K	normally closed	3,3	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0340X10	K	2 mm steps	3,4	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0340X16	K	normally closed	3,4	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0350X10	K	2 mm steps	3,5	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0350X16	K	normally closed	3,5	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0360X10	K	2 mm steps	3,6	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0360X16	K	normally closed	3,6	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0370X10	K	2 mm steps	3,7	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0370X16	K	normally closed	3,7	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0380X10	K	2 mm steps	3,8	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0380X16	K	normally closed	3,8	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0390X10	K	2 mm steps	3,9	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0390X16	K	normally closed	3,9	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0400X10	K	2 mm steps	4	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	65°
08920-K0400X16	K	normally closed	4	8	15	4,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	65°

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-K0410X12	K	2 mm steps	4,1	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	65°
08920-K0410X20	K	normally closed	4,1	10	18	6,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	65°
08920-K0410X25	K	0.052	4,1	10	18	6,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	65°
08920-K0420X12	K	2 mm steps	4,2	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	65°
08920-K0420X20	K	normally closed	4,2	10	18	6,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	65°
08920-K0420X25	K	0.052	4,2	10	18	6,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	65°
08920-K0430X12	K	2 mm steps	4,3	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	65°
08920-K0430X20	K	normally closed	4,3	10	18	6,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	65°
08920-K0430X25	K	0.052	4,3	10	18	6,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	65°
08920-K0440X12	K	2 mm steps	4,4	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	65°
08920-K0440X20	K	normally closed	4,4	10	18	6,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	65°
08920-K0440X25	K	0.052	4,4	10	18	6,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	65°
08920-K0450X12	K	2 mm steps	4,5	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	65°
08920-K0450X20	K	normally closed	4,5	10	18	6,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	65°
08920-K0450X25	K	0.052	4,5	10	18	6,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	65°
08920-K0460X12	K	2 mm steps	4,6	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	65°
08920-K0460X20	K	normally closed	4,6	10	18	6,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	65°
08920-K0460X25	K	0.052	4,6	10	18	6,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	65°
08920-K0470X12	K	2 mm steps	4,7	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	65°
08920-K0470X20	K	normally closed	4,7	10	18	6,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	65°
08920-K0470X25	K	0.052	4,7	10	18	6,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	65°
08920-K0480X12	K	2 mm steps	4,8	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	65°
08920-K0480X20	K	normally closed	4,8	10	18	6,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	65°
08920-K0480X25	K	0.052	4,8	10	18	6,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	65°
08920-K0490X12	K	2 mm steps	4,9	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-K0620X25	K	0.052	6,2	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0630X12	K	2 mm steps	6,3	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0630X20	K	normally closed	6,3	12	22	8,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0630X25	K	0.052	6,3	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0640X12	K	2 mm steps	6,4	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0640X20	K	normally closed	6,4	12	22	8,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0640X25	K	0.052	6,4	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0650X12	K	2 mm steps	6,5	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0650X20	K	normally closed	6,5	12	22	8,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0650X25	K	0.052	6,5	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0660X12	K	2 mm steps	6,6	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0660X20	K	normally closed	6,6	12	22	8,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0660X25	K	0.052	6,6	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0670X12	K	2 mm steps	6,7	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0670X20	K	normally closed	6,7	12	22	8,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0670X25	K	0.052	6,7	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0680X12	K	2 mm steps	6,8	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0680X20	K	normally closed	6,8	12	22	8,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0680X25	K	0.052	6,8	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0690X12	K	2 mm steps	6,9	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0690X20	K	normally closed	6,9	12	22	8,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0690X25	K	0.052	6,9	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0700X12	K	2 mm steps	7	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0700X20	K	normally closed	7	12	22	8,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	60°
08920-K0700X25	K	0.052	7	12	22	8,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20</	

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-K0840X28	K	normally closed	8,4	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0840X36	K	0.052	8,4	15	26	10,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	50°
08920-K0850X16	K	2 mm steps	8,5	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	50°
08920-K0850X28	K	normally closed	8,5	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0850X36	K	0.052	8,5	15	26	10,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	50°
08920-K0860X16	K	2 mm steps	8,6	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	50°
08920-K0860X28	K	normally closed	8,6	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0860X36	K	0.052	8,6	15	26	10,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	50°
08920-K0870X16	K	2 mm steps	8,7	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	50°
08920-K0870X28	K	normally closed	8,7	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0870X36	K	0.052	8,7	15	26	10,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	50°
08920-K0880X16	K	2 mm steps	8,8	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	50°
08920-K0880X28	K	normally closed	8,8	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0880X36	K	0.052	8,8	15	26	10,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	50°
08920-K0890X16	K	2 mm steps	8,9	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	50°
08920-K0890X28	K	normally closed	8,9	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0890X36	K	0.052	8,9	15	26	10,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	50°
08920-K0900X16	K	2 mm steps	9	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	50°
08920-K0900X28	K	normally closed	9	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0900X36	K	0.052	9	15	26	10,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	50°
08920-K0910X16	K	2 mm steps	9,1	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	50°
08920-K0910X28	K	normally closed	9,1	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0910X36	K	0.052	9,1	15	26	10,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	50°
08920-K0920X16	K	2 mm steps	9,2	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	50°
08920-K0920X28	K	normally closed	9,2	15	26	10,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	50°
08920-K0920X3																			

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-K1060X16	K	2 mm steps	10,6	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°
08920-K1060X28	K	normally closed	10,6	18	30	12,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	50°
08920-K1060X36	K	0.052	10,6	18	30	12,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	50°
08920-K1070X16	K	2 mm steps	10,7	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°
08920-K1070X28	K	normally closed	10,7	18	30	12,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	50°
08920-K1070X36	K	0.052	10,7	18	30	12,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	50°
08920-K1080X16	K	2 mm steps	10,8	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°
08920-K1080X28	K	normally closed	10,8	18	30	12,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	50°
08920-K1080X36	K	0.052	10,8	18	30	12,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	50°
08920-K1090X16	K	2 mm steps	10,9	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°
08920-K1090X28	K	normally closed	10,9	18	30	12,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	50°
08920-K1090X36	K	0.052	10,9	18	30	12,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	50°
08920-K1100X16	K	2 mm steps	11	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°
08920-K1100X28	K	normally closed	11	18	30	12,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	50°
08920-K1100X36	K	0.052	11	18	30	12,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	50°
08920-K1110X16	K	2 mm steps	11,1	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°
08920-K1110X28	K	normally closed	11,1	18	30	12,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	50°
08920-K1110X36	K	0.052	11,1	18	30	12,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	50°
08920-K1120X16	K	2 mm steps	11,2	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°
08920-K1120X28	K	normally closed	11,2	18	30	12,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	50°
08920-K1120X36	K	0.052	11,2	18	30	12,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	50°
08920-K1130X16	K	2 mm steps	11,3	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°
08920-K1130X28	K	normally closed	11,3	18	30	12,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	50°
08920-K1130X36	K	0.052	11,3	18	30	12,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	50°
08920-K1140X16	K	2 mm steps	11,4	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	50°</

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-K1270X45	K	0.052	12,7	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1280X20	K	2 mm steps	12,8	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1280X36	K	normally closed	12,8	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1280X45	K	0.052	12,8	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1290X20	K	2 mm steps	12,9	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1290X36	K	normally closed	12,9	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1290X45	K	0.052	12,9	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1300X20	K	2 mm steps	13	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1300X36	K	normally closed	13	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1300X45	K	0.052	13	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1310X20	K	2 mm steps	13,1	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1310X36	K	normally closed	13,1	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1310X45	K	0.052	13,1	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1320X20	K	2 mm steps	13,2	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1320X36	K	normally closed	13,2	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1320X45	K	0.052	13,2	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1330X20	K	2 mm steps	13,3	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1330X36	K	normally closed	13,3	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1330X45	K	0.052	13,3	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1340X20	K	2 mm steps	13,4	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1340X36	K	normally closed	13,4	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1340X45	K	0.052	13,4	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1350X20	K	2 mm steps	13,5	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1350X36	K	normally closed	13,5	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1350X45	K	0.05																	

Overview of items

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-K1490X36	K	normally closed	14,9	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1490X45	K	0.052	14,9	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1500X20	K	2 mm steps	15	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1500X36	K	normally closed	15	22	34	15,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1500X45	K	0.052	15	22	34	15,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	35°
08920-K1550X20	K	2 mm steps	15,5	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	35°
08920-K1550X36	K	normally closed	15,5	26	39	19	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	35°
08920-K1550X45	K	0.052	15,5	26	39	19	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	35°
08920-K1600X20	K	2 mm steps	16	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	35°
08920-K1600X36	K	normally closed	16	26	39	19	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	35°
08920-K1600X45	K	0.052	16	26	39	19	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	35°
08920-K1650X20	K	2 mm steps	16,5	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	35°
08920-K1650X36	K	normally closed	16,5	26	39	19	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	35°
08920-K1650X45	K	0.052	16,5	26	39	19	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	35°
08920-K1700X20	K	2 mm steps	17	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	35°
08920-K1700X36	K	normally closed	17	26	39	19	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	35°
08920-K1700X45	K	0.052	17	26	39	19	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	35°
08920-K1750X20	K	2 mm steps	17,5	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	35°
08920-K1750X36	K	normally closed	17,5	26	39	19	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	35°
08920-K1750X45	K	0.052	17,5	26	39	19	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	35°
08920-K1800X20	K	2 mm steps	18	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	35°
08920-K1800X36	K	normally closed	18	26	39	19	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	35°
08920-K1800X45	K	0.052	18	26	39	19	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	35°
08920-K1850X25	K	2 mm steps	18,5	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K1850X45	K	normally closed	18,5	30	46	23	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K1850X56	K	0.052	18,5	30	46	23	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K1900X25	K	2 mm steps	19	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K1900X45	K	normally closed	19	30	46	23	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K1900X56	K	0.052	19	30	46	23	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K1950X25	K	2 mm steps	19,5	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K1950X45	K	normally closed	19,5	30	46	23	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K1950X56	K	0.052	19,5	30	46	23	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2000X25	K	2 mm steps	20	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2000X45	K	normally closed	20	30	46	23	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2000X56	K	0.052	20	30	46	23	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2050X25	K	2 mm steps	20,5	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2050X45	K	normally closed	20,5	30	46	23	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2050X56	K	0.052	20,5	30	46	23	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2100X25	K	2 mm steps	21	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2100X45	K	normally closed	21	30	46	23	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2100X56	K	0.052	21	30	46	23	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2150X25	K	2 mm steps	21,5	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2150X45	K	normally closed	21,5	30	46	23	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2150X56	K	0.052	21,5	30	46	23	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2200X25	K	2 mm steps	22	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2200X45	K	normally closed	22	30	46	23	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2200X56	K	0.052	22	30	46	23	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	30°
08920-K2250X25	K	2 mm steps	22,5	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2250X45	K	normally closed	22,5	35	52	27	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2250X56	K	0.052	22,5	35	52	27	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2300X25	K	2 mm steps	23	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2300X45	K	normally closed	23	35	52	27	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2300X56	K	0.052	23	35	52	27	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2350X25	K	2 mm steps	23,5	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2350X45	K	normally closed	23,5	35	52	27	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2350X56	K	0.052	23,5	35	52	27	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2400X25	K	2 mm steps	24	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2400X45	K	normally closed	24	35	52	27	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2400X56	K	0.052	24	35	52	27	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2450X25	K	2 mm steps	24,5	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2450X45	K	normally closed	24,5	35	52	27	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2450X56	K	0.052	24,5	35	52	27	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2500X25	K	2 mm steps	25	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2500X45	K	normally closed	25	35	52	27	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2500X56	K	0.052	25	35	52	27	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	30°

Overview of items

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-K2550X25	K	2 mm steps	25,5	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2550X45	K	normally closed	25,5	35	52	27	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2550X56	K	0.052	25,5	35	52	27	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2600X25	K	2 mm steps	26	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2600X45	K	normally closed	26	35	52	27	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2600X56	K	0.052	26	35	52	27	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	30°
08920-K2650X30	K	2 mm steps	26,5	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	30°
08920-K2650X56	K	normally closed	26,5	42	59	31	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	30°
08920-K2650X67	K	0.052	26,5	42	59	31	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	30°
08920-K2700X30	K	2 mm steps	27	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	30°
08920-K2700X56	K	normally closed	27	42	59	31	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	30°
08920-K2700X67	K	0.052	27	42	59	31	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	30°
08920-K2750X30	K	2 mm steps	27,5	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	30°
08920-K2750X56	K	normally closed	27,5	42	59	31	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	30°
08920-K2750X67	K	0.052	27,5	42	59	31	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	30°
08920-K2800X30	K	2 mm steps	28	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	30°
08920-K2800X56	K	normally closed	28	42	59	31	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	30°
08920-K2800X67	K	0.052	28	42	59	31	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	30°
08920-K2850X30	K	2 mm steps	28,5	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	30°
08920-K2850X56	K	normally closed	28,5	42	59	31	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	30°
08920-K2850X67	K	0.052	28,5	42	59	31	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	30°
08920-K2900X30	K	2 mm steps	29	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	30°
08920-K2900X56	K	normally closed	29	42	59	31	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	30°
08920-K2900X67	K	0.052	29	42	59	31	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	30°
08920-K2950X30	K	2 mm steps	29,5	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	30°
08920-K2950X56	K	normally closed	29,5	42	59	31	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	30°
08920-K2950X67	K	0.052	29,5	42	59	31	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	30°
08920-K3000X30	K	2 mm steps	30	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	30°
08920-K3000X56	K	normally closed	30	42	59	31	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	30°
08920-K3000X67	K	0.052	30	42	59	31	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	30°
08920-L0240X10	L	2 mm steps	2,4	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0240X16	L	normally closed	2,4	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0250X10	L	2 mm steps	2,5	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0250X16	L	normally closed	2,5	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0260X10	L	2 mm steps	2,6	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0260X16	L	normally closed	2,6	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0270X10	L	2 mm steps	2,7	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0270X16	L	normally closed	2,7	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0280X10	L	2 mm steps	2,8	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0280X16	L	normally closed	2,8	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0290X10	L	2 mm steps	2,9	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0290X16	L	normally closed	2,9	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0300X10	L	2 mm steps	3	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0300X16	L	normally closed	3	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0310X10	L	2 mm steps	3,1	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0310X16	L	normally closed	3,1	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0320X10	L	2 mm steps	3,2	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0320X16	L	normally closed	3,2	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0330X10	L	2 mm steps	3,3	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0330X16	L	normally closed	3,3	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0340X10	L	2 mm steps	3,4	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0340X16	L	normally closed	3,4	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0350X10	L	2 mm steps	3,5	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0350X16	L	normally closed	3,5	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0360X10	L	2 mm steps	3,6	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0360X16	L	normally closed	3,6	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0370X10	L	2 mm steps	3,7	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0370X16	L	normally closed	3,7	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0380X10	L	2 mm steps	3,8	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0380X16	L	normally closed	3,8	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0390X10	L	2 mm steps	3,9	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0390X16	L	normally closed	3,9	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0400X10	L	2 mm steps	4	8	15	-	2,5	10	8	3	-	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0400X16	L	normally closed	4	8	15	D1+0,5	2,5	16	8	3	6	4,25	0,02	0,005	1,5	7	11,5	15	-
08920-L0410X12	L	2 mm steps	4,1	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-L0410X20	L	normally closed	4,1	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0410X25	L	0.052	4,1	10	18	D1+0,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	-
08920-L0420X12	L	2 mm steps	4,2	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-
08920-L0420X20	L	normally closed	4,2	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0420X25	L	0.052	4,2	10	18	D1+0,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	-
08920-L0430X12	L	2 mm steps	4,3	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-
08920-L0430X20	L	normally closed	4,3	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0430X25	L	0.052	4,3	10	18	D1+0,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	-
08920-L0440X12	L	2 mm steps	4,4	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-
08920-L0440X20	L	normally closed	4,4	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0440X25	L	0.052	4,4	10	18	D1+0,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	-
08920-L0450X12	L	2 mm steps	4,5	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-
08920-L0450X20	L	normally closed	4,5	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0450X25	L	0.052	4,5	10	18	D1+0,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	-
08920-L0460X12	L	2 mm steps	4,6	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-
08920-L0460X20	L	normally closed	4,6	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0460X25	L	0.052	4,6	10	18	D1+0,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	-
08920-L0470X12	L	2 mm steps	4,7	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-
08920-L0470X20	L	normally closed	4,7	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0470X25	L	0.052	4,7	10	18	D1+0,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	-
08920-L0480X12	L	2 mm steps	4,8	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-
08920-L0480X20	L	normally closed	4,8	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0480X25	L	0.052	4,8	10	18	D1+0,5	2,5	25	8	3	13	4,25	0,02	0,005	2	7	13	17	-
08920-L0490X12	L	2 mm steps	4,9	10	18	-	2,5	12	8	3	-	4,25	0,02	0,005	2	7	13	17	-
08920-L0490X20	L	normally closed	4,9	10	18	D1+0,5	2,5	20	8	3	8	4,25	0,02	0,005	2	7	13	17	-
08920-L0490X25	L																		

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-L0630X12	L	2 mm steps	6,3	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0630X20	L	normally closed	6,3	12	22	D1+0,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0630X25	L	0.052	6,3	12	22	D1+0,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0640X12	L	2 mm steps	6,4	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0640X20	L	normally closed	6,4	12	22	D1+0,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0640X25	L	0.052	6,4	12	22	D1+0,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0650X12	L	2 mm steps	6,5	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0650X20	L	normally closed	6,5	12	22	D1+0,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0650X25	L	0.052	6,5	12	22	D1+0,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0660X12	L	2 mm steps	6,6	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0660X20	L	normally closed	6,6	12	22	D1+0,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0660X25	L	0.052	6,6	12	22	D1+0,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0670X12	L	2 mm steps	6,7	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0670X20	L	normally closed	6,7	12	22	D1+0,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0670X25	L	0.052	6,7	12	22	D1+0,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0680X12	L	2 mm steps	6,8	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0680X20	L	normally closed	6,8	12	22	D1+0,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0680X25	L	0.052	6,8	12	22	D1+0,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0690X12	L	2 mm steps	6,9	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0690X20	L	normally closed	6,9	12	22	D1+0,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0690X25	L	0.052	6,9	12	22	D1+0,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0700X12	L	2 mm steps	7	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0700X20	L	normally closed	7	12	22	D1+0,5	3	20	10	4	8	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0700X25	L	0.052	7	12	22	D1+0,5	3	25	10	4	13	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0710X12	L	2 mm steps	7,1	12	22	-	3	12	10	4	-	6	0,02	0,005	2	8,5	16,5	20	-
08920-L0710X20	L	normally closed	7,1</																

Overview of items

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-L0840X36	L	0.052	8,4	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0850X16	L	2 mm steps	8,5	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0850X28	L	normally closed	8,5	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0850X36	L	0.052	8,5	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0860X16	L	2 mm steps	8,6	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0860X28	L	normally closed	8,6	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0860X36	L	0.052	8,6	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0870X16	L	2 mm steps	8,7	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0870X28	L	normally closed	8,7	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0870X36	L	0.052	8,7	15	26	-	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0880X16	L	2 mm steps	8,8	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0880X28	L	normally closed	8,8	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0880X36	L	0.052	8,8	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0890X16	L	2 mm steps	8,9	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0890X28	L	normally closed	8,9	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0890X36	L	0.052	8,9	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0900X16	L	2 mm steps	9	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0900X28	L	normally closed	9	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0900X36	L	0.052	9	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0910X16	L	2 mm steps	9,1	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0910X28	L	normally closed	9,1	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0910X36	L	0.052	9,1	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0920X16	L	2 mm steps	9,2	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0920X28	L	normally closed	9,2	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0920X36	L	0.052	9,2	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0930X16	L	2 mm steps	9,3	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0930X28	L	normally closed	9,3	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0930X36	L	0.052	9,3	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0940X16	L	2 mm steps	9,4	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0940X28	L	normally closed	9,4	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0940X36	L	0.052	9,4	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0950X16	L	2 mm steps	9,5	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0950X28	L	normally closed	9,5	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0950X36	L	0.052	9,5	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0960X16	L	2 mm steps	9,6	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0960X28	L	normally closed	9,6	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0960X36	L	0.052	9,6	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0970X16	L	2 mm steps	9,7	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0970X28	L	normally closed	9,7	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0970X36	L	0.052	9,7	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0980X16	L	2 mm steps	9,8	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0980X28	L	normally closed	9,8	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0980X36	L	0.052	9,8	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L0990X16	L	2 mm steps	9,9	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L0990X28	L	normally closed	9,9	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L0990X36	L	0.052	9,9	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L1000X16	L	2 mm steps	10	15	26	-	3	16	10	4	-	6	0,02	0,005	2	8,5	18	22	-
08920-L1000X28	L	normally closed	10	15	26	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	18	22	-
08920-L1000X36	L	0.052	10	15	26	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	18	22	-
08920-L1010X16	L	2 mm steps	10,1	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1010X28	L	normally closed	10,1	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1010X36	L	0.052	10,1	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1020X16	L	2 mm steps	10,2	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1020X28	L	normally closed	10,2	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1020X36	L	0.052	10,2	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1030X16	L	2 mm steps	10,3	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1030X28	L	normally closed	10,3	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1030X36	L	0.052	10,3	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1040X16	L	2 mm steps	10,4	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1040X28	L	normally closed	10,4	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1040X36	L	0.052	10,4	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1050X16	L	2 mm steps	10,5	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1050X28	L	normally closed	10,5	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1050X36	L	0.052	10,5	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1060X16	L	2 mm steps	10,6	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-L1060X28	L	normally closed	10,6	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1060X36	L	0.052	10,6	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1070X16	L	2 mm steps	10,7	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1070X28	L	normally closed	10,7	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1070X36	L	0.052	10,7	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1080X16	L	2 mm steps	10,8	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1080X28	L	normally closed	10,8	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1080X36	L	0.052	10,8	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1090X16	L	2 mm steps	10,9	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1090X28	L	normally closed	10,9	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1090X36	L	0.052	10,9	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1100X16	L	2 mm steps	11	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1100X28	L	normally closed	11	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1100X36	L	0.052	11	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1110X16	L	2 mm steps	11,1	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1110X28	L	normally closed	11,1	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1110X36	L	0.052	11,1	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1120X16	L	2 mm steps	11,2	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1120X28	L	normally closed	11,2	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1120X36	L	0.052	11,2	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1130X16	L	2 mm steps	11,3	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1130X28	L	normally closed	11,3	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1130X36	L	0.052	11,3	18	30	D1+0,5	3	36	10	4	20	6	0,02	0,005	2	8,5	20	24	-
08920-L1140X16	L	2 mm steps	11,4	18	30	-	3	16	10	4	-	6	0,02	0,005	2	8,5	20	24	-
08920-L1140X28	L	normally closed	11,4	18	30	D1+0,5	3	28	10	4	12	6	0,02	0,005	2	8,5	20	24	-
08920-L1140X36	L	0.052	11,4	18</															

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-L1280X20	L	2 mm steps	12,8	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1280X36	L	normally closed	12,8	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1280X45	L	0.052	12,8	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1290X20	L	2 mm steps	12,9	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1290X36	L	normally closed	12,9	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1290X45	L	0.052	12,9	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1300X20	L	2 mm steps	13	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1300X36	L	normally closed	13	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1300X45	L	0.052	13	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1310X20	L	2 mm steps	13,1	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1310X36	L	normally closed	13,1	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1310X45	L	0.052	13,1	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1320X20	L	2 mm steps	13,2	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1320X36	L	normally closed	13,2	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1320X45	L	0.052	13,2	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1330X20	L	2 mm steps	13,3	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1330X36	L	normally closed	13,3	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1330X45	L	0.052	13,3	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1340X20	L	2 mm steps	13,4	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1340X36	L	normally closed	13,4	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1340X45	L	0.052	13,4	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1350X20	L	2 mm steps	13,5	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1350X36	L	normally closed	13,5	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1350X45	L	0.052	13,5	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1360X20	L	2 mm steps	13,6	22	34	-	5	20	12	5,5</									

Overview of items

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-L1490X45	L	0.052	14,9	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1500X20	L	2 mm steps	15	22	34	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1500X36	L	normally closed	15	22	34	D1+0,5	5	36	12	5,5	16	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1500X45	L	0.052	15	22	34	D1+0,5	5	45	12	5,5	25	7	0,02	0,005	3	10,5	23,5	28	-
08920-L1550X20	L	2 mm steps	15,5	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	-
08920-L1550X36	L	normally closed	15,5	26	39	D1+1,0	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	-
08920-L1550X45	L	0.052	15,5	26	39	D1+1,0	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	-
08920-L1600X20	L	2 mm steps	16	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	-
08920-L1600X36	L	normally closed	16	26	39	D1+1,0	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	-
08920-L1600X45	L	0.052	16	26	39	D1+1,0	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	-
08920-L1650X20	L	2 mm steps	16,5	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	-
08920-L1650X36	L	normally closed	16,5	26	39	D1+1,0	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	-
08920-L1650X45	L	0.052	16,5	26	39	D1+1,0	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	-
08920-L1700X20	L	2 mm steps	17	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	-
08920-L1700X36	L	normally closed	17	26	39	D1+1,0	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	-
08920-L1700X45	L	0.052	17	26	39	D1+1,0	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	-
08920-L1750X20	L	2 mm steps	17,5	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	-
08920-L1750X36	L	normally closed	17,5	26	39	D1+1,0	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	-
08920-L1750X45	L	0.052	17,5	26	39	D1+1,0	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	-
08920-L1800X20	L	2 mm steps	18	26	39	-	5	20	12	5,5	-	7	0,02	0,005	3	10,5	26	31	-
08920-L1800X36	L	normally closed	18	26	39	D1+1,0	5	36	12	5,5	16	7	0,02	0,005	3	10,5	26	31	-
08920-L1800X45	L	0.052	18	26	39	D1+1,0	5	45	12	5,5	25	7	0,02	0,005	3	10,5	26	31	-
08920-L1850X25	L	2 mm steps	18,5	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	-
08920-L1850X45	L	normally closed	18,5	30	46	D1+1,0	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	-
08920-L1850X56	L	0.052	18,5	30	46	D1+1,0	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	-
08920-L1900X25	L	2 mm steps	19	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	-
08920-L1900X45	L	normally closed	19	30	46	D1+1,0	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	-
08920-L1900X56	L	0.052	19	30	46	D1+1,0	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	-
08920-L1950X25	L	2 mm steps	19,5	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	-
08920-L1950X45	L	normally closed	19,5	30	46	D1+1,0	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	-
08920-L1950X56	L	0.052	19,5	30	46	D1+1,0	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2000X25	L	2 mm steps	20	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2000X45	L	normally closed	20	30	46	D1+1,0	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2000X56	L	0.052	20	30	46	D1+1,0	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2050X25	L	2 mm steps	20,5	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2050X45	L	normally closed	20,5	30	46	D1+1,0	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2050X56	L	0.052	20,5	30	46	D1+1,0	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2100X25	L	2 mm steps	21	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2100X45	L	normally closed	21	30	46	D1+1,0	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2100X56	L	0.052	21	30	46	D1+1,0	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2150X25	L	2 mm steps	21,5	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2150X45	L	normally closed	21,5	30	46	D1+1,0	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2150X56	L	0.052	21,5	30	46	D1+1,0	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2200X25	L	2 mm steps	22	30	46	-	5	25	12	5,5	-	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2200X45	L	normally closed	22	30	46	D1+1,0	5	45	12	5,5	20	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2200X56	L	0.052	22	30	46	D1+1,0	5	56	12	5,5	31	7	0,02	0,005	3	10,5	29,5	35	-
08920-L2250X25	L	2 mm steps	22,5	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2250X45	L	normally closed	22,5	35	52	D1+1,0	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2250X56	L	0.052	22,5	35	52	D1+1,0	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2300X25	L	2 mm steps	23	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2300X45	L	normally closed	23	35	52	D1+1,0	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2300X56	L	0.052	23	35	52	D1+1,0	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2350X25	L	2 mm steps	23,5	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2350X45	L	normally closed	23,5	35	52	D1+1,0	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2350X56	L	0.052	23,5	35	52	D1+1,0	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2400X25	L	2 mm steps	24	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2400X45	L	normally closed	24	35	52	D1+1,0	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2400X56	L	0.052	24	35	52	D1+1,0	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2450X25	L	2 mm steps	24,5	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2450X45	L	normally closed	24,5	35	52	D1+1,0	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2450X56	L	0.052	24,5	35	52	D1+1,0	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2500X25	L	2 mm steps	25	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2500X45	L	normally closed	25	35	52	D1+1,0	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2500X56	L	0.052	25	35	52	D1+1,0	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2550X25	L	2 mm steps	25,5	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	-

Overview of items

Order No.	Form	Product type	D1	D2	D3	D4	D6	L1	L2	L6	L7	M	T1	T2	R1	R2	E1	E2	α
08920-L2550X45	L	normally closed	25,5	35	52	D1+1,0	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2550X56	L	0.052	25,5	35	52	D1+1,0	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2600X25	L	2 mm steps	26	35	52	-	6	25	12	5,5	-	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2600X45	L	normally closed	26	35	52	D1+1,0	6	45	12	5,5	20	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2600X56	L	0.052	26	35	52	D1+1,0	6	56	12	5,5	31	7	0,04	0,008	3	10,5	32,5	37	-
08920-L2650X30	L	2 mm steps	26,5	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	-
08920-L2650X56	L	normally closed	26,5	42	59	D1+1,0	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	-
08920-L2650X67	L	0.052	26,5	42	59	D1+1,0	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	-
08920-L2700X30	L	2 mm steps	27	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	-
08920-L2700X56	L	normally closed	27	42	59	D1+1,0	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	-
08920-L2700X67	L	0.052	27	42	59	D1+1,0	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	-
08920-L2750X30	L	2 mm steps	27,5	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	-
08920-L2750X56	L	normally closed	27,5	42	59	D1+1,0	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	-
08920-L2750X67	L	0.052	27,5	42	59	D1+1,0	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	-
08920-L2800X30	L	2 mm steps	28	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	-
08920-L2800X56	L	normally closed	28	42	59	D1+1,0	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	-
08920-L2800X67	L	0.052	28	42	59	D1+1,0	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	-
08920-L2850X30	L	2 mm steps	28,5	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	-
08920-L2850X56	L	normally closed	28,5	42	59	D1+1,0	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	-
08920-L2850X67	L	0.052	28,5	42	59	D1+1,0	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	-
08920-L2900X30	L	2 mm steps	29	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	-
08920-L2900X56	L	normally closed	29	42	59	D1+1,0	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	-
08920-L2900X67	L	0.052	29	42	59	D1+1,0	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	-
08920-L2950X30	L	2 mm steps	29,5	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	-
08920-L2950X56	L	normally closed	29,5	42	59	D1+1,0	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	-
08920-L2950X67	L	0.052	29,5	42	59	D1+1,0	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	-
08920-L3000X30	L	2 mm steps	30	42	59	-	6	30	12	5,5	-	7	0,04	0,008	3	10,5	36	41	-
08920-L3000X56	L	normally closed	30	42	59	D1+1,0	6	56	12	5,5	26	7	0,04	0,008	3	10,5	36	41	-
08920-L3000X67	L	0.052	30	42	59	D1+1,0	6	67	12	5,5	37	7	0,04	0,008	3	10,5	36	41	-

Information about this article

DIN 173 replaceable drill bushes, Part 1

The DIN 173 replaceable drill bush allows you to quickly and easily change drilling diameters so that the time is used for the actual precision work and not for exchanging equipment. The practical fixture on the DIN 173 bush makes the Form K a quick-change bush for right-hand cutting tools.

Our replaceable drill bushes are hardened to 780 ± 40 HV 10 and ground and have the diameter and tolerance engraved on the upper flange face.

The replaceable bushes are especially practical when used together with a DIN 173 drill bush clamp, DIN 912 socket head screws and DIN 173 flat head screw. The bayonet lock is secured using a DIN 173-1 drill bush clamp together with a DIN 912 socket head screw.