

## Item description/product images



## Description

**Material:**

Clamping bolt, steel;  
clamping ring, brass


**Version:**

Clamping bolt, hardened and black oxidised.  
Clamping ring, bright.

**Note:**

The clamping bolts can be fixed to the machine table directly with T-slot nuts.  
Clamping parallel to the table is guaranteed by low tolerance classes (js6) for the height.  
The clamping range is 8 – 40 mm. Clamping screws for the ranges 40 – 67 and 65 – 87 mm are also available.  
The intermediate plate prevents damage to the machine table, as well as shifting during tightening. The brass clamping ring prevents impressions on the workpiece.

## Drawings



## Overview of items

Order No.	H	Clamp range
04395-050	50	8-40
04395-100	100	8-40