

Item description/product images



Description

**Material, version:**  
Robust metal housing, chromium-plated

**Note:**  
Standard clamping shank Ø 8h6  
Measuring range 10 mm  
Scale graduation 0.01 mm  
Spindle travel 1 mm per revolution of large pointer  
Housing Ø 58 mm  
Rotation counter  
Tolerance marks

Overview of items

Order No.	Version
32540-01	dial gauge
32540-012	dial gauge with calibration certificate