


Item description/product images

**Description****Material:**

Foot plate polyamide
Threaded spindle stainless steel.
Anti-slip plate (NBR) Shore 70.

Version:

Foot plate blue RAL 5005.
Threaded spindle bright.
Anti-slip plate, black.

Note:

Levelling feet with stainless steel spindle, polyamide base and optional anti-slip plate. The anti-slip plate absorbs vibrations and prevents the swivel foot slipping.

The load values specified in the table are based on a test series, in which a static load was applied perpendicular to the plates through the centre of the spindle. Radially acting forces, such as those produced by vibrations or other shaking effects, affect the load rating and are not taken into account for the specified values.

On request:


Threaded spindle stainless steel 1.4401.
Foot plate black.
with 30° tilt.

Accessory:

Hex nuts 07212.

Drawing reference:

Form A without anti-slip plate
Form B with anti-slip plate



Overview of items

Order No.	Form	D	D1	H	H1	H2	L	SW	Load rating max. kN (static load only)
27792-10-12106512X100	A	65	M12	29	139	39	100	10	13
27792-10-12106512X150	A	65	M12	29	189	39	150	10	13
27792-10-12106512X50	A	65	M12	29	89	39	50	10	13
27792-10-12106516X100	A	65	M16	29	139	39	100	13	18
27792-10-12106516X150	A	65	M16	29	189	39	150	13	18
27792-10-12106516X200	A	65	M16	29	239	39	200	13	18
27792-10-12108316X100	A	83	M16	25	135	35	100	13	20
27792-10-12108316X150	A	83	M16	25	185	35	150	13	20
27792-10-12108316X200	A	83	M16	25	235	35	200	13	20
27792-10-12108320X100	A	83	M20	25	137	37	100	17	20
27792-10-12108320X150	A	83	M20	25	187	37	150	17	20
27792-10-12108320X200	A	83	M20	25	237	37	200	17	20
27792-10-12110316X100	A	103	M16	27	137	37	100	13	30
27792-10-12110316X150	A	103	M16	27	187	37	150	13	30
27792-10-12110316X200	A	103	M16	27	237	37	200	13	30
27792-10-12110320X100	A	103	M20	27	139	39	100	17	30
27792-10-12110320X150	A	103	M20	27	189	39	150	17	30
27792-10-12110320X200	A	103	M20	27	239	39	200	17	30
27792-10-12110324X100	A	103	M24	27	139	39	100	20	30
27792-10-12110324X150	A	103	M24	27	189	39	150	20	30
27792-10-12110324X200	A	103	M24	27	239	39	200	20	30