

Item description/product images



Description

Material:

Steel.

Version:

Thrust pin steel, hardened and electro zinc-plated.

Sleeve blue electro zinc-plated.

Note:


Lateral spring plungers with threaded sleeve can be individually adjusted to suit the the part being held. The threaded sleeve is also suitable for screwing into thin sheet metal as it can be fastened with one or two nuts.

W and Z are customer specified.

Drawing reference:

1) assembly tool

Drawings



Overview of items

Order No.	Version 2	Component material	L	L1	D	D1	±S	F ca.N	X	SW	K	Order No. assembly tool
03334-1020X12	without seal	steel	11,5	6,7	M12	5	0,8	20	1,6	10	2x60°	03334-06

Overview of items

Order No.	Version 2	Component material	L	L1	D	D1	±S	F ca.N	X	SW	K	Order No. assembly tool
03334-1020X20	without seal	steel	19	6,7	M12	5	0,8	20	1,6	10	2x60°	03334-06
03334-1020X27	without seal	steel	26,5	6,7	M12	5	0,8	20	1,6	10	2x60°	03334-06
03334-1050X12	without seal	steel	11,5	6,7	M12	5	0,8	50	1,6	10	2x60°	03334-06
03334-1050X20	without seal	steel	19	6,7	M12	5	0,8	50	1,6	10	2x60°	03334-06
03334-1050X27	without seal	steel	26,5	6,7	M12	5	0,8	50	1,6	10	2x60°	03334-06
03334-1100X12	without seal	steel	11,5	6,7	M12	5	0,8	100	1,6	10	2x60°	03334-06
03334-1100X20	without seal	steel	19	6,7	M12	5	0,8	100	1,6	10	2x60°	03334-06
03334-1100X27	without seal	steel	26,5	6,7	M12	5	0,8	100	1,6	10	2x60°	03334-06
03334-1040X12	without seal	steel	11,5	10,7	M12	6	1	40	1,8	10	2x60°	03334-06
03334-1040X20	without seal	steel	19	10,7	M12	6	1	40	1,8	10	2x60°	03334-06
03334-1040X27	without seal	steel	26,5	10,7	M12	6	1	40	1,8	10	2x60°	03334-06
03334-1075X12	without seal	steel	11,5	10,7	M12	6	1	75	1,8	10	2x60°	03334-06
03334-1075X20	without seal	steel	19	10,7	M12	6	1	75	1,8	10	2x60°	03334-06
03334-1075X27	without seal	steel	26,5	10,7	M12	6	1	75	1,8	10	2x60°	03334-06
03334-1150X12	without seal	steel	11,5	10,7	M12	6	1	100	1,8	10	2x60°	03334-06
03334-1150X20	without seal	steel	19	10,7	M12	6	1	100	1,8	10	2x60°	03334-06
03334-1150X27	without seal	steel	26,5	10,7	M12	6	1	100	1,8	10	2x60°	03334-06
03334-1100X16	without seal	steel	18	16,7	M18X1,5	10	1,6	100	3,2	16	2,5x60°	03334-10
03334-1100X29	without seal	steel	31,5	16,7	M18X1,5	10	1,6	100	3,2	16	2,5x60°	03334-10
03334-1100X43	without seal	steel	45	16,7	M18X1,5	10	1,6	100	3,2	16	2,5x60°	03334-10
03334-1200X16	without seal	steel	18	16,7	M18X1,5	10	1,6	150	3,2	16	2,5x60°	03334-10
03334-1200X29	without seal	steel	31,5	16,7	M18X1,5	10	1,6	150	3,2	16	2,5x60°	03334-10
03334-1200X43	without seal	steel	45	16,7	M18X1,5	10	1,6	150	3,2	16	2,5x60°	03334-10
03334-1300X16	without seal	steel	18	16,7	M18X1,5	10	1,6	200	3,2	16	2,5x60°	03334-10
03334-1300X29	without seal	steel	31,5	16,7	M18X1,5	10	1,6	200	3,2	16	2,5x60°	03334-10
03334-1300X43	without seal	steel	45	16,7	M18X1,5	10	1,6	200	3,2	16	2,5x60°	03334-10