



Item description/product images



lift to
disengage



Description

Material:

Handle steel 1.0401.

All other steel parts grade 5.8.

Version:

Handle painted silver-grey hammer-tone.

Steel parts black oxidised.

Note for ordering:

Screws from 70 mm long have 60 mm long threads.

Note:

For other dimensions see clamping levers with internal threads.

On request:


Other threads, screw lengths and special versions.

Dimension "H1" available in other lengths at extra charge.

Drawing reference:

1) flat point DIN EN ISO 4753

Drawings



Overview of items

Clamping Levers, Classic ball style, steel, with male thread

Order No.	Main material	Size	X	D	D1	D2	H	H1	H3	H4	A	A1	No. of teeth	L
06441-1A4X20	steel	1	3/8-16	19	28	20	40,5	12	65	68,5	83	107	24	20
06441-1A4X30	steel	1	3/8-16	19	28	20	40,5	12	65	68,5	83	107	24	30
06441-1A4X40	steel	1	3/8-16	19	28	20	40,5	12	65	68,5	83	107	24	40
06441-1A4X45	steel	1	3/8-16	19	28	20	40,5	12	65	68,5	83	107	24	45
06441-1A4X50	steel	1	3/8-16	19	28	20	40,5	12	65	68,5	83	107	24	50
06441-1A4X60	steel	1	3/8-16	19	28	20	40,5	12	65	68,5	83	107	24	60
06441-1A5X20	steel	1	1/2-13	19	28	20	40,5	12	65	68,5	83	107	24	20
06441-1A5X30	steel	1	1/2-13	19	28	20	40,5	12	65	68,5	83	107	24	30
06441-1A5X40	steel	1	1/2-13	19	28	20	40,5	12	65	68,5	83	107	24	40
06441-1A5X45	steel	1	1/2-13	19	28	20	40,5	12	65	68,5	83	107	24	45
06441-1A5X50	steel	1	1/2-13	19	28	20	40,5	12	65	68,5	83	107	24	50
06441-1A5X60	steel	1	1/2-13	19	28	20	40,5	12	65	68,5	83	107	24	60

Overview of items

Order No.	Main material	Size	X	D	D1	D2	H	H1	H3	H4	A	A1	No. of teeth	L
06441-2A5X25	steel	2	1/2-13	23	35	25	51,5	12	79,5	84	108	138,5	26	25
06441-2A5X30	steel	2	1/2-13	23	35	25	51,5	12	79,5	84	108	138,5	26	30
06441-2A5X40	steel	2	1/2-13	23	35	25	51,5	12	79,5	84	108	138,5	26	40
06441-2A5X45	steel	2	1/2-13	23	35	25	51,5	12	79,5	84	108	138,5	26	45
06441-2A5X50	steel	2	1/2-13	23	35	25	51,5	12	79,5	84	108	138,5	26	50
06441-2A5X60	steel	2	1/2-13	23	35	25	51,5	12	79,5	84	108	138,5	26	60
06441-2A6X25	steel	2	5/8-11	23	35	25	51,5	12	79,5	84	108	138,5	26	25
06441-2A6X30	steel	2	5/8-11	23	35	25	51,5	12	79,5	84	108	138,5	26	30
06441-2A6X40	steel	2	5/8-11	23	35	25	51,5	12	79,5	84	108	138,5	26	40
06441-2A6X45	steel	2	5/8-11	23	35	25	51,5	12	79,5	84	108	138,5	26	45
06441-2A6X50	steel	2	5/8-11	23	35	25	51,5	12	79,5	84	108	138,5	26	50
06441-2A6X60	steel	2	5/8-11	23	35	25	51,5	12	79,5	84	108	138,5	26	60
06441-3A6X30	steel	3	5/8-11	30	43	30	60	12	93	97,5	132	168	36	30
06441-3A6X40	steel	3	5/8-11	30	43	30	60	12	93	97,5	132	168	36	40
06441-3A6X50	steel	3	5/8-11	30	43	30	60	12	93	97,5	132	168	36	50
06441-3A6X60	steel	3	5/8-11	30	43	30	60	12	93	97,5	132	168	36	60
06441-3A7X30	steel	3	3/4-10	30	43	30	60	12	93	97,5	132	168	36	30
06441-3A7X40	steel	3	3/4-10	30	43	30	60	12	93	97,5	132	168	36	40
06441-3A7X50	steel	3	3/4-10	30	43	30	60	12	93	97,5	132	168	36	50
06441-3A7X60	steel	3	3/4-10	30	43	30	60	12	93	97,5	132	168	36	60