

Item description/product images



Description

Material:

Crank aluminium.

Cylinder grip thermoplastic and steel.

Version:

Crank black powder-coated.

Thermoplastic black grey.


Steel parts black oxidised.

Note:

Similar to DIN 469.

Versions with transverse bore are secured using the ISO 4027 (DIN 914) grub screw.

Drawings



Overview of items

Order No.	Version 1	Version 2	A	D	D2	D3	D7	H	H1	H2	H3	H4	L
06503-1110	Cam-action indexing plungers	DIN 39	80	24	10	16	-	89	49	22	13,4	-	100
06503-1212	Cam-action indexing plungers	DIN 39	100	28	12	20	-	108	59,5	26	16	-	124
06503-1314	Cam-action indexing plungers	DIN 39	125	30	14	25	-	140	83	28	15,8	-	153
06503-1417	Cam-action indexing plungers	DIN 39	160	34	17	25	-	144	83	32	19,6	-	190
06503-11106	Cam-action indexing plungers	Clamp	80	24	10	16	M6	89	49	22	13,4	7,5	100
06503-12126	Cam-action indexing plungers	Clamp	100	28	12	20	M6	107,9	59,4	26	16	7,5	124
06503-13146	Cam-action indexing plungers	Clamp	125	30	14	26	M6	140,5	83,5	28	15,8	7,5	153
06503-14176	Cam-action indexing plungers	Clamp	160	34	17	26	M6	144,5	83,5	32	19,6	7,5	190

Order No.	Version 1	Version 2	A	D	D3	D7	H	H1	H2	H3	H4	L	SW
06503-2110	Clamping claws	DIN 39	80	24	16	-	89	49	22	13,4	-	100	10
06503-2212	Clamping claws	DIN 39	100	28	20	-	108	59,5	26	16	-	124	12
06503-2314	Clamping claws	DIN 39	125	30	25	-	140	83	28	15,8	-	153	14
06503-2417	Clamping claws	DIN 39	160	34	25	-	144	83	32	19,6	-	190	17
06503-21106	Clamping claws	Clamp	80	24	16	M6	89	49	22	13,4	7,5	100	10
06503-22126	Clamping claws	Clamp	100	28	20	M6	107,9	59,4	26	16	7,5	124	12
06503-23146	Clamping claws	Clamp	125	30	26	M6	140,5	83,5	28	15,8	7,5	153	14
06503-24176	Clamping claws	Clamp	160	34	26	M6	144,5	83,5	32	19,6	7,5	190	17

