

Item description/product images



Description

Material:

Crank stainless steel 1.4308.

Cylindrical grip thermoplastic and stainless steel 1.4404.

Version:

Crank bright.

Thermoplastic black grey.


Stainless steel bright.

Note:

Similar to DIN 469.

Versions with transverse bore are secured using the ISO 4027 (DIN 914) grub screw.

Drawings



Overview of items

Order No.	Version 1	Version 2	A	D	D2	D3	D7	H	H1	H2	H3	H4	L	SW
06506-3110	Cam-action indexing plungers	DIN 39	80	24	10	16	-	71,1	49,1	22	13,4	-	100	-
06506-3212	Cam-action indexing plungers	DIN 39	100	28	12	20	-	87,4	61,4	26	16	-	124	-
06506-3314	Cam-action indexing plungers	DIN 39	125	30	14	26	-	110,5	82,5	28	15,8	-	153	-
06506-3417	Cam-action indexing plungers	DIN 39	160	34	17	26	-	114,5	82,5	32	19,6	-	190	-
06506-31106	Cam-action indexing plungers	ChromLine clamping joints	80	24	10	16	M6	71,1	49,1	22	13,4	7,5	100	-
06506-32126	Cam-action indexing plungers	ChromLine clamping joints	100	28	12	20	M6	87,4	61,4	26	16	7,5	124	-
06506-33146	Cam-action indexing plungers	ChromLine clamping joints	125	30	14	26	M6	110,5	82,5	28	15,8	7,5	153	-
06506-34176	Cam-action indexing plungers	ChromLine clamping joints	160	34	17	26	M6	114,5	82,5	32	19,6	7,5	190	-
06506-4110	Clamping claws	DIN 39	80	24	-	16	-	71,1	49,1	22	13,4	-	100	10
06506-4212	Clamping claws	DIN 39	100	28	-	20	-	87,4	61,4	26	16	-	124	12
06506-4314	Clamping claws	DIN 39	125	30	-	26	-	110,5	82,5	28	15,8	-	153	14
06506-4417	Clamping claws	DIN 39	160	34	-	26	-	114,5	82,5	32	19,6	-	190	17
06506-41106	Clamping claws	ChromLine clamping joints	80	24	-	16	M6	71,1	49,1	22	13,4	7,5	100	10
06506-42126	Clamping claws	ChromLine clamping joints	100	28	-	20	M6	87,4	61,4	26	16	7,5	124	12

Overview of items

Order No.	Version 1	Version 2	A	D	D2	D3	D7	H	H1	H2	H3	H4	L	SW
06506-43146	Clamping claws	ChromLine clamping joints	125	30	-	26	M6	110,5	82,5	28	15,8	7,5	153	14
06506-44176	Clamping claws	ChromLine clamping joints	160	34	-	26	M6	114,5	82,5	32	19,6	7,5	190	17