


Item description/product images



Description

Material:

Housing stainless steel or nickel-plated brass.
Active face PBT or PA 12.

Version:

Voltage: $U = 10 - 30 \text{ V DC}$
Function: Normally open
Switch type: PNP
Mounting type: flush
Security type: IP 67

Note:

Non-contact, wear-free operation. High switching frequency and switch accuracy.
Non-sensitive to vibration, dust and moisture. Inductive sensors register all metals without contact.

Short-circuit and reverse-polarity proof.

Temperature range:

$-25 \text{ }^{\circ}\text{C}$ to $+70 \text{ }^{\circ}\text{C}$

Safety:

This product is not suited as a sensor for the personal protection.

Drawing reference:


1) LED-indicator

P = cable length


BN = brown

BK = black

BU = blue



Drawings



Overview of items

Order No.	Main material	Form	G	L	L1	P	Material active surface	Switching distance S_n (mm)	Current I max. (mA)	Switching frequency f (Hz)	Connection type	No. of conductors x conductor cross-section
83000-10-010X5000	250 ml spray	A	M8x1	30	-	5000	PBT	1,5	200	3000	0.07	3 x 0,14 mm ²
83000-10-020	250 ml spray	B	M8x1	45	34,5	-	PBT	2	200	1500	0.079	-
83000-10-030	250 ml spray	B	M8x1	55	44,5	-	PBT	2	200	1500	0.079	-
83000-10-040	560 mm / M10x1.25 / M8	B	M8x1	59	50	-	PA 12	1,5	200	1000	0.079	-
83000-10-050	560 mm / M10x1.25 / M8	B	M8x1	59	50	-	PA 12	2	200	700	0.079	-
83000-10-060	560 mm / M10x1.25 / M8	B	M12x1	65	50	-	PA 12	2	200	1200	0.079	-
83000-10-070	560 mm / M10x1.25 / M8	B	M12x1	65	50	-	PA 12	4	200	500	0.079	-

Overview of items

Order No.	Main material	Form	G	L	L1	P	Material active surface	Switching distance Sn (mm)	Current I max. (mA)	Switching frequency f (Hz)	Connection type	No. of conductors x conductor cross-section
83000-10-080X300	2-piece	C	M5X0,5	27	-	300	PBT	0,8	100	5000	0.079	-