

Item description/product images



Description

Material:

Hinge steel.
Spacer washer brass.
Hinge pin steel or brass.


Version:

Grease nipple DIN 71412-D, electro zinc-plated steel.
Steel parts, bright.

Note:

The hinges are made of weldable profile steel.
The pin is fixed into the lower part of the hinge.
The differing steel qualities of the weld and the beam onto which the hinge is welded must be at least equal to or better than:
S235 JR+AR acc. to EN 10025-2:2004-10
DIN 8563 part 3 or Fe E 235 acc. to SIA 161

Drawings



Overview of items

Order No.	Form	Component material	A	B	D	D1
27885-008040012	A	0.0042	9,7	40	8	5
27885-008050012	A	0.0042	9,7	50	8	5
27885-010060012	A	0.0042	12,7	60	10	6
27885-010070012	A	0.0042	12	70	10	6
27885-013080012	A	0.0042	15,5	80	13	8
27885-016100012	A	0.0042	20	100	16	10
27885-016120012	A	0.0042	20	120	16	11
27885-018135012	A	0.0042	22	135	18	12
27885-020150012	A	0.0042	25	150	20	13
27885-020180012	A	0.0042	25	180	20	14
27885-023200012	A	0.0042	28,5	200	23	16
27885-008040022	A	560 mm / M10x1.25 / M8	9,7	40	8	5
27885-008050022	A	560 mm / M10x1.25 / M8	9,7	50	8	5
27885-010060022	A	560 mm / M10x1.25 / M8	12,7	60	10	6
27885-010070022	A	560 mm / M10x1.25 / M8	12	70	10	6
27885-013080022	A	560 mm / M10x1.25 / M8	15,5	80	13	8
27885-016100022	A	560 mm / M10x1.25 / M8	20	100	16	10

Overview of items

Order No.	Form	Component material	A	B	D	D1
27885-016120022	A	560 mm / M10x1.25 / M8	20	120	16	11
27885-018135022	A	560 mm / M10x1.25 / M8	22	135	18	12
27885-020150022	A	560 mm / M10x1.25 / M8	25	150	20	13
27885-020180022	A	560 mm / M10x1.25 / M8	25	180	20	14
27885-023200022	A	560 mm / M10x1.25 / M8	28,5	200	23	16
27885-113080012	B	0.0042	16	80	13	8
27885-116100012	B	0.0042	20	100	16	10
27885-116120012	B	0.0042	20	120	16	10
27885-118135012	B	0.0042	22,5	135	18	12
27885-120150012	B	0.0042	25,5	150	20	13
27885-120180012	B	0.0042	25	180	20	14
27885-123200012	B	0.0042	29	200	23	16